TECHNICIAN AIDS

FLUORESCENT MAGNIFYING WORK LAMP

- UL/CSA Approved
- Steel Balanced 45" Extension Arm
- Adjustment Spring Tension Knobs at all joints
- 3 Conductor AC cord 120V AC / 60 Hz
- Precise 3 Diopter Lens
- Supplied with 22W Fluorescent Circular Tube
- Durable Baked Enamel Finish (White)
- Extra Strength Steel and Die Cast Base and Clamp
- Packaged in Four Color Box

REPLACEMENT PARTS

No. SLR115 - Replacement Bulb No. SLR116 - Rocker Switch Assembly No. SLR119 - 3 Diopter Lens No. SLR120 - 5 Diopter Lens No. SLR121 - Counter Base No. SLR117 - C Clamp No. SLR118 - Base (Transformer Housing) No. SLR123 - Adjustable "C" Clamp

No. SL114

No. SLR124 - AC Receptacle for base Housing

This fine, precision product is excellent for inspection of printed circuit boards and inspection of any fine detail work. A must for the technician, the laboratory and the production line. Will clamp to any drafting board or work surface up to 2-1/4" thickness.

HOOK-ON Test Prods Completely INSULATED



The injector-type prods that firmly clip onto large or small components for testing purposes. OBJECT: Meter reading for any required length of time while hands are free for other work.

No. 450 - Our most popular standard size, 2-1/4" long. Set of two: BLACK and RED No. 450B-BLK - bulk, black No. 450B-BLU - bulk, blue No. 450B-GRN - bulk, green No. 450B-RED - bulk, red No. 450B-WHT - bulk, white No. 450B-YEL - bulk, yellow No. 4504 - Set of four: BLACK, RED, GREEN and YELLOW No. 4506 - Set of six: BLACK, BLUE, GREEN, RED, WHITE and YELLOW No. 450S - This mini clip is ideal for those crowded, hard-to-get-at circuits, 1-9/16" long. Set of two: BLACK and RED No. 450SB-BLK - bulk, black No. 450SB-BLU - bulk, blue No. 450SB-GRN - bulk, green No. 450SB-RED - bulk, red No. 450SB-WHT - bulk, white No. 450SB-YEL - bulk, yellow No. 4504S - Set of four: BLACK, RED, GREEN and YELLOW No. 4506S - Set of six: BLACK, BLUE, GREEN, RED, WHITE and YELLOW

STACKABLE BANANA PLUGS

This quick design from Philmore allows user to assemble own test lead sets with quick assembly stackable design. Just insert wire into handle, solder to plug/jack assembly and snap together. Available in five colors.



No. BP1000B - bulk, black No. BP1002B - bulk, red No. BP1004B - bulk, yellow No. BP1006B - bulk, green No. BP1008B - bulk, blue

No. BP1010 - (1) red and black, display packaged No. BP1014 - (1) red, black, yellow and green, display packaged

IC TEST LEAD SET

5 color-coded, 16" test leads with miniature hook-on prods at both ends. A must for technicians and experimenters who want temporary interconnects with out danger of shorting.

Colors: Red, black, yellow, green, white



No. 500

INCANDESCENT MAGNIFYING LAMP

- UL Approved
- Steel 39" extension arm: Properly balanced for easy maneuverability and positioning.
- · Springs with adjustable tensioning knobs at all joints.
- 18 AWG/2 Conductor SPT-1 AC cord with polarized plug. 120V/60Hz.
- 3-3/4" Diameter lens with magnification lens of 3x (3 diopter).
- Uses standard 60 watt household light bulb (not included).
- Attractive, durable white molded housing, base and clamp.

