


ANTENNA HARDWARE

WALL MOUNT


Made of heavy gauge steel. Supplied with 2 brackets and mounting hardware. For masts up to 1-1/2" diameter. Wall clearance of 3-3/4".



No. 15-9023

CHIMNEY MOUNT

fits masts up to 1-1/2" diameter complete with heavy duty strap clamps, 18 ft. stainless steel strapping and necessary hardware.



No. 15-1218

UNIVERSAL INSULATOR (STANDOFF) Woodscrew Type




No. 15-853 - 3-1/2" Long (4 Per Package)

No. 15-854 - 5-1/2" Long (4 Per Package)

MASONRY DRIVE-IN STANDOFFS

Universal Insulator - Hardened steel with 3" nail. Double welded construction.



No. 15-820 - (2 Per Package)

MAST STANDOFFS


Universal Insulator - Snap Type for 1-1/4" Masts



No. 15-822 - (2 Per Package)

STRAP-ON STANDOFFS

Universal Insulator 10" Straps



No. 15-823 - 10" Straps (2 Per Package)

ANTENNA GUY WIRE


50 ft. - 6 Strand - 20 Gauge wire. Heavy Galvanized Steel. Rustproof.



No. 15-620

GROUND ROD

Heavy Gauge Steel Rod with tapered tip 3/8" dia. Copper Plated with ground wire clamp.




No. 15-929 - 4 ft. (20 Pcs. / Ctn.)

No. 15-916 - 6 ft. (20 Pcs. / Ctn.)

ROTOR WIRE

3 Conductor
UL Listed




No. 15-127 - 50 ft.

No. 15-128 - 75 ft.

No. 15-129 - 100 ft.

2-WAY GUY WIRE MAST CLAMP


Two screw eyes for attaching guy wire to masts up to 1-1/2" diameter.



No. 15-827 - (1 Per Package)

CABLE CLAMPS

Guy wire clamps to hold wires securely. Galvanized Steel - 1/8" wire size.
No. 15-850 - (4 Per Package)



GUY RING and CLAMP For 1-1/4" Diameter Masts

No. 15-835



SCREW HOOK


Steel - Zinc Plated
1/4" x 3-3/4" - 1" I.D.



No. 15-825 - (3 Per Package)

LAG SCREWS

Steel slotted hex washer head lag screw. (1/4" x 2") For installation of TV antenna mounts and brackets.




No. 15-833 - (4 Per Package)

MAST CLAMP ASSEMBLY

U Bolt Assembly. Serrated edges to prevent twisting.

No. 15-826 - (1 Per Package)



TURNBUCKLES

Galvanized steel for installing guy wires. Closed 4" - Open 5-5/8"

No. 15-829 - (2 Per Package)

