

## 18 AWG SPT-1 PARALLEL POWER CORD UL listed


### SPECIFICATIONS:

**AWG Gauge:** 18 Gauge copper  
**Stranding:** 41 strands/ 34 Gauge  
**Insulation Thickness:** 0.030"  
**Insulation Material:** PVC

**Working Voltage:** 300V AC  
**Temperature Range:** 105°C  
**Size:**  
**Nominal O.D.:** 2.65 x 5.35mm or .104" x .210"  
**UL Listed CSA Approved**



A standard insulated, two conductor cord with a rib on one conductor for polarity indication. Available in popular colors. The 25 foot lengths are supplied in blister display packages. The longer lengths are supplied on spools with a clear, protective shrink-wrap.



COLOR	25 ft.	100 ft.	250 ft.	1000 ft.	2000 ft.
Black	48-142	48-102	48-252	48-1002	48-2002
Brown	48-144	48-104	48-254	48-1004	48-2004
White	48-146	48-106	48-256	48-1006	48-2006

## TRIPLE EXTENSION CORD

UL Listed

Unbreakable - All Vinyl

#18 Gauge wire - SPT1 AC plug to triple socket  
 Plugs and connectors are molded in matching color vinyl.  
 Connectors have safety adaptor for protection.



No. 8405B - Brown, 9 ft.      No. 8405V - White, 9 ft.  
 No. 8406B - Brown, 15 ft.      No. 8406V - White, 15 ft.

## AC CORD SET

for Cassette Recorders

A direct replacement for the new Panasonic Cassette Recorders, as well as for other recorders and many portable TV sets. Mates with male receptacles having 3/32" diameter pins on 0.275" centers. Rated 7 amps at 125V AC, this cord set is UL Approved. 6 feet long.

No. 2464P

No. 2464PB bulk packaged

No. 2465P - Replacement power cord for Sony recorders and boom boxes

No. 2465PB bulk packaged



No. 2464P



No. 2465P



## AC POWER CORD SETS for OEM and Replacements

SPT cord sets are typically used in light duty applications, such as table radios, household lamps and so forth. SPT cords are two conductor, 18 gauge. SJT cord sets are three conductor, counting the ground wire, and regarded as hard service cord sets, frequently used with bench tools such as grinders, saws etc.. this is a popular cord set for equipment of all kinds. SJT cord sets are supplied with a standard NEMA 5-15P power plug. Both of these series are of fully molded construction, the plug and cord are permanently connected.



Top: SPT Type AC Cords  
 Bottom: SJT Type AC Cords

Part No.	UL Wire Type	Wire Gauge	Length	Color	Amps
SPT1182-6BL	SPT-1	18 x 2	6 ft.	Black	10
SPT1182-6BR	SPT-1	18 x 2	6 ft.	Brown	10
SPT1182-6WH	SPT-1	18 x 2	6 ft.	White	10
SPT1182-9BL	SPT-1	18 x 2	9 ft.	Black	10
SPT1182-9BR	SPT-1	18 x 2	9 ft.	Brown	10
SJT143-3	SJT	14 X 3	3 ft.	Black	15
SJT143-6	SJT	14 x 3	6 ft.	Black	15
SJT163-3	SJT	16 x 3	3 ft.	Black	15
SJT163-6	SJT	16 x 3	6 ft.	Black	13
SJT163-9	SJT	16 x 3	9 ft.	Black	13
SJT183-6	SJT	18 x 3	6 ft.	Black	10
SJT183-9	SJT	18 x 3	9 ft.	Black	10