


Pan-Pouch™ and Pocket Pouch Telephone Cable Identification Kits and Pan-Ty® Miniature Cable Ties

Panduit offers a fast, convenient method for identifying telephone cable binder groups on both sides of a splice in PIC Cable. Miniature cross section Pan-Ty® Cable Ties in 25 color combinations match the universally accepted Even-Count Color Code. Solid color cable ties are available for identification of Super Groups in cable containing more than 600 pairs. Cable ties have a maximum bundle diameter of 0.82 inches (21mm). Each 50 piece package fits into Pan-Pouch™ or Pocket Pouch Kits.



Part Number	Description	Std. Pkg. Qty.
PPC25x50F	Pan-Pouch™ Kit <ul style="list-style-type: none"> Filled with 1,250 miniature cable ties (50 each of 24 striped ties and 50 solid red ties) Folds for easy storage Hang from cable by using integral hook and loop fasteners An eyelet permits hanging from nails or hooks 2 ply laminated black nylon/vinyl 10.5" x 38" (267mm x 965mm) <ul style="list-style-type: none"> Folded size: 10.5" x 6" (266mm x 152mm) 	1
PPC25x50	Empty Pan-Pouch™ Kit	1



Part Number	Description	Std. Pkg. Qty.
PP5x50F	Pan-Pouch™ Kit <ul style="list-style-type: none"> Filled with 250 miniature cable ties (five 50 piece packages: blue, orange, green, brown, and slate – all with white stripe) Belt loop and snap closure White/clear vinyl 3.5" x 5.25" (89mm x 133mm) 	1


Cable Ties for Pan-Pouch™ and Pocket Pouch Kits

Cable Ties for Pan-Pouch™ and Pocket Pouch Kits



Panduit® Pan-Ty® Miniature cross section cable ties come in convenient packages of 50 each with perforated, tear-off tops sized to fit into the individual pockets of the Pan-Pouch™ and Pocket Pouch Kits.

These one-piece, all nylon cable ties accommodate a maximum bundle diameter of 0.82" (21mm).



Ordering information

Part Number	Cable Tie Color	Stripe Color	Packaging	
			Std. Pkg. Qty.	Std. Ctn. Qty.
PLT1M-L6-10	Blue	White	50	1000
PLT1M-L3-10	Orange		50	1000
PLT1M-L5-10	Green		50	1000
PLT1M-L1-10	Brown		50	1000
PLT1M-L8-10	Slate		50	1000
PLT1M-L6-2	Blue	Red	50	1000
PLT1M-L3-2	Orange		50	1000
PLT1M-L5-2	Green		50	1000
PLT1M-L1-2	Brown		50	1000
PLT1M-L8-2	Slate		50	1000
PLT1M-L6-0	Blue	Black	50	1000
PLT1M-L3-0	Orange		50	1000
PLT1M-L5-0	Green		50	1000
PLT1M-L1-0	Brown		50	1000
PLT1M-L8-0	Slate		50	1000

Part Number	Cable Tie Color	Stripe Color	Packaging	
			Std. Pkg. Qty.	Std. Ctn. Qty.
PLT1M-L6-4	Blue	Yellow	50	1000
PLT1M-L3-4	Orange		50	1000
PLT1M-L5-4	Green		50	1000
PLT1M-L1-4	Brown		50	1000
PLT1M-L8-4	Slate		50	1000
PLT1M-L6-7	Blue	Violet	50	1000
PLT1M-L3-7	Orange		50	1000
PLT1M-L5-7	Green		50	1000
PLT1M-L1-7	Brown		50	1000
PLT1M-L8-7	Slate		50	1000
PLT1M-L2	Red	—	50	1000
PLT1M-L0	Black*		50	1000
PLT1M-L4Y	Yellow*		50	1000
PLT1M-L6	Blue*	—	50	1000
PLT1M-L3	Orange*		50	1000
PLT1M-L5	Green*		50	1000
PLT1M-L1	Brown*		50	1000
PLT1M-L8	Slate*		50	1000

*Not included in filled Pan-Pouch™ Kit – P/N: PPC25x50F.

Dimensions are in inches [Dimensions in brackets are metric]

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2016 Panduit Corp.
ALL RIGHTS RESERVED.
CTCB46--WW-ENG
Replaces WW-CTCB19
3/2016