



**Part Number:** 83030600  
**Description:** IEC 60320 Sheet F Screw Mount Power Outlet

[Previous](#)

[Next](#)



**\*\* Please select your country for pricing and availability \*\***

Select the country you are located in

## Specifications

*(Specifications subject to change without notice)*

<b>Part Number:</b> 83030600
<b>Int'l Current Rating:</b> 10A
<b>Int'l Voltage Rating:</b> 250VAC
<b>N.A. Current Rating:</b> 15A
<b>N.A. Voltage Rating :</b> 250VAC
<b>Temperature Rating:</b> -20°C to 70°C
<b>Flammability Rating:</b> UL 94 V-0
<b>Class:</b> I
<b>Quick Disconnects:</b> 3
<b>Terminal Material:</b> Tin-plated brass
<b>Sheet Style:</b> Sheet F
<b>Mounting Style:</b> Screw
<b>General Material:</b> PBT
<b>Color:</b> Black
<b>CE Marking:</b> yes
<b>REMARKS:</b> Static Environmental Temp Rating -20°C to 70°C. QD are 6.3mm
<b>Last Modification:</b> 05/20/16 • 08:48:33 • netui <b>*Specifications subject to change without notice</b>



Printer-friendly version

Printable version of Specifications

Document Center			
Drawings	Approvals	Environmental	Misc.
AutoCAD (.dwg)			Designer Notes
Adobe Acrobat PDF (.pdf)			
ISO-10303 STEP Product Data (.step)	Click to email approval documents		
3D ACIS Model (.sat)			
International Graphics Exchange Standard File Format (.igs)			
Adobe Acrobat 3D (.pdf)			

## Related Items



55010190 - Brown PVC Single Wire



55010450 - Green PVC Single Wire



55011570 - White PVC Single Wire



83030600 - IEC 60320 Sheet F Screw Mount Power Outlet

### United States

PO Box 115 | Oskaloosa, IA 52577 | [info@interpower.com](mailto:info@interpower.com)  
 Toll-Free Phone: (800) 662-2290 | Toll-Free Fax: (800) 645-5360  
 Phone: (641) 673-5000 | Fax: (641) 673-5100

### United Kingdom

10 Kelvin Drive | Knowlhill, Milton Keynes | Buckinghamshire, MK5 8NH | UK | [uk@interpower.com](mailto:uk@interpower.com)  
**UK, Ireland, Germany, Switzerland, Austria**  
 Freephone: 00800 5566 5566 | Freefax: 00800 5655 5655  
**International:** Phone: +44 (0)1908 295 300 | Fax: +44 (0)1908 295301