

Search our website...

Quest part no. search

» Store » Wall Mount Enclosures » New Products » 200 Series Wall Mount Enclosure

## 200 Series Wall Mount Enclosure



|                                      |   |
|--------------------------------------|---|
| Rack Size Height External (Internal) | RU Lbs.<br>5U 130 12.5" (9")<br>7U 130 16" (12.5")<br>9U 130 19.5" (16")<br>11U 130 23" (19.5")<br>14U 130 28" (24.5")<br>16U 130 31.5" (28")<br>20U 130 38.5" (35")<br>28U 130 52.5" (49") |
| Rack Size Width External (Internal)  | 21" (19")   |
| Rack Size Depth External (Internal)  | 5U-16U: 20" (16") 20U-28U: 28" (24")  |
| Mounting Format (Internal)           | 19"   |
| Reversible Front Locking Door        | Smoked Acrylic  |
| Vented Side Panels                   | Removable   |
| Hinged Swing Out Design              | No  |
| Reinforced Door Frame                | Yes   |
| Cage Nut Rails                       | Front & Rear  |
| Cage Nuts, Screws & Washers          | 12  |
| Key Lock Set (2 Keys per Set)        | 1 Set   |
| Cable Access                         | Top:Cutouts Bottom:Cutouts  |
| Structure & Fabrication              | 18AWG Steel   |
| Electrostatic Powdercoat MicroFinish | Black (-02) Ivory (-01)   |
| Preinstalled 80CFM 110V Fans         | 1   |
| Compliance                           | EIA-310D  |
| Delivery Style                       | Assembled   |

[Click to Enlarge](#)



Like 0 Tweet +139 Share 139 Share

**LIVE CHAT / SUPPORT**  
M-F 8AM - 5:30PM EST (USA)  
**ONLINE**

**LIVE CHAT / SUPPORT**  
M-F 8AM - 5:30PM EST (USA)  
**ONLINE**

**LIVE CHAT / SUPPORT**  
M-F 8AM - 5:30PM EST (USA)  
**ONLINE**

**QUEST SELECT**

- QUEST TECHNOLOGY INT'L
- QUEST MANUFACTURING
- QUEST FACTORY OUTLET
- LOCJACK
- PREMIERE RACEWAY

**DISTRIBUTOR LOCATOR**

**AFFILIATIONS**

[Items](#) [Description](#) [Features](#) [Spec Sheets](#) [Video](#)

| SKU                           | Ship Weight | Color | Ext. Dimensions | Inches | Rack Units | UPC         |
|-------------------------------|-------------|-------|-----------------|--------|------------|-------------|
| <a href="#">WM2019-05-02</a>  | 39 lbs.     | Black | 21"w x 20"d     | 13"    | 5U         | 80011802092 |
| <a href="#">WM2019-07-02</a>  | 43 lbs.     | Black | 21"w x 20"d     | 16"    | 7U         | 80011802094 |
| <a href="#">WM2019-09-02</a>  | 47 lbs.     | Black | 21"w x 20"d     | 20"    | 9U         | 80011802096 |
| <a href="#">WM2019-09-02D</a> | 47 lbs.     | Black | 21"w x 20"d     | 20"    | 9U         | 80011802272 |
| <a href="#">WM2019-11-02</a>  | 52 lbs.     | Black | 21"w x 20"d     | 23"    | 11U        | 80011802098 |
| <a href="#">WM2019-11-02D</a> | 53 lbs.     | Black | 21"w x 20"d     | 20"    | 11U        | 80011802273 |
| <a href="#">WM2019-14-02</a>  | 57 lbs.     | Black | 21"w x 20"d     | 28"    | 14U        | 80011802100 |
| <a href="#">WM2019-16-02</a>  | 61 lbs.     | Black | 21"w x 20"d     | 32"    | 16U        | 80011802102 |
| <a href="#">WM2019-20-02</a>  | 70 lbs.     | Black | 21"w x 28"d     | 39"    | 20U        | 80011802261 |
| <a href="#">WM2019-28-02</a>  | 86 lbs.     | Black | 21"w x 28"d     | 53"    | 28U        | 80011802262 |

Related Items:



#12-24 Phillips  
Head Mounting  
Screws



[» details](#)

Horizontal PDU  
Surge Strip, 12  
Front 120VAC/15A  
EMI/RFI Outlets  
with 6ft Swiveling  
Power Cord



[» details](#)

19 inch Horizontal  
Non-Vented Filler  
Panel



[» details](#)



#### Customer Service

- » [Contact Us](#)
- » [Sales Support](#)
- » [Custom Requests](#)
- » [Help/FAQ's](#)
- » [Distributor Finder](#)

#### Technical Support

- » [Training Resources](#)
- » [Cross Reference](#)
- » [How-To Video's](#)
- » [Installation Instructions](#)
- » [Product Search](#)
- » [Industry Resources](#)

#### Marketing

- » [New Products](#)
- » [Press Releases](#)
- » [Product Literature](#)
- » [Catalog Downloads](#)
- » [Trade Show Schedule](#)
- » [Close-Out Specials](#)

#### Company Information

- » [Company Contacts](#)
- » [About Quest](#)
- » [Warranty Information](#)
- » [Certifications](#)
- » [Company Affiliations](#)

#### Join Our Mailing List

#### Social Media

