



**Supplement
Product Catalog
Q502**



Fig. 1



Fig. 2



Fig. 3

In addition to the complete line of professional installation tools already offered, Quest has now added a new RF ratchet crimp tool frame that comes without die sets giving installers the choice of purchasing individual die sets to fit their specific requirements. This tool is offered in conjunction with a new series of interchangeable die sets, which are offered for many cable and connector types. As an accessory product, newly offered are thumbscrew sets, which replace the traditional die screws and gives the user the ability to quickly remove and interchange different dies securely.

PRO RF RATCHET CRIMP TOOL W/O DIES

ITEM #	DESCRIPTION	FIG.
TRF-1000	PROFESSIONAL RATCHET CRIMP TOOL W/O DIES	1

THUMBSCREW SETS

ITEM #	DESCRIPTION	FIG.
TRS-1000	THUMBSCREW SET FOR TRF RF CRIMP TOOL SERIES 2	

DIE SET FOR TRF SERIES RF CRIMP TOOLS

ITEM #	DESCRIPTION	FIG.
TRD-3000	TRF SERIES DIE SET .255/.213/.068 HEX SIZES	3
TRD-3001	TRF SERIES DIE SET .305/.228/.068 HEX SIZES	3
TRD-3010	TRF SERIES DIE SET .213/.190/.068/.042 HEX SIZES	3
TRD-3015	TRF SERIES DIE SET .255/.213/.068/.042 HEX SIZES	3
TRD-3020	TRF SERIES DIE SET .350/.320/.255 HEX SIZES	3
TRD-3030	TRF SERIES DIE SET .429/.100 HEX SIZES	3
TRD-3035	TRF SERIES DIE SET .213/.178/.068/.042 HEX SIZES	3
TRD-3040	TRF SERIES DIE SET .324/.265/.068/.042 HEX SIZES	3
TRD-3045	TRF SERIES DIE SET .324/.178/.068 HEX SIZES	3
TRD-3051	TRF SERIES DIE SET 10-22 AWG INSULATED TERM.	3
TRD-3054	TRF SERIES DIE SET 12-22 AWG NON-INS. TERM.	3

Please see Quest Full Line Catalog #Q700 for complete interconnect products



The QUEST Professional Ratchet Crimp Tool series provides installers the best choice in professional connector crimp tools. These tools are designed for durable use and provides long life dependability and consistent, reliable terminations, crimp after crimp. They feature a 10" frame design, which allows increased leverage during the crimp process with a ratchet action mechanism providing easy, repeatable and reliable crimps. The tools come complete with die sets, which are also interchangeable. **Lifetime warranted.**

RATCHET CRIMP TOOL

ITEM #	DESCRIPTION	FIG.
TRF-3060	PROFESSIONAL UNIVERSAL RATCHET CRIMP TOOL WITH DIES .325 / .255 / .213 / .110 / .068	1

D-SUB CONTACT CRIMP TOOLS

ITEM #	DESCRIPTION	FIG.
TRF-4000	RATCHET PRO GRADE CONTACT CRIMPER FOR D-SUB MINIATURE OPEN BARREL CONTACTS, V.35 CONTACTS AND NON-INSULATED PINS-18-22 AWG, 24-30 AWG WITH TENSION ADJUSTMENT.	2
TFC-5000	NON-RATCHET CRIMP TOOL FOR OPEN BARREL D-SUB CONTACTS 20-24-28 AWG-WITH CUTTER	3

REPLACEMENT BLADES FOR STRIPPERS & TOOLS

ITEM #	DESCRIPTION	FIG.
TSB-5000	REPLACEMENT BLADE FOR TCS-5000	N/S
TSB-5010	REPLACEMENT BLADE FOR TCS-5010	N/S
TSB-5020	BLADE SET FOR TCS-5020	N/S
TSB-5021	RED 3-STEP BLADE SET FOR TCS-5020	N/S
TSB-5022	GREEN 2-STEP BLADE SET FOR TCS-5020	N/S
TSB-5023	BLUE 2-STEP BLADE SET FOR TCS-5020	N/S
TSB-6000	REPLACEMENT BLADES FOR TEL-6000 CRIMPER	N/S
TSB-6001	REPLACEMENT BLADES FOR TEL-6001 CRIMPER	N/S

Please see Quest Full Line Catalog #Q700 for complete interconnect products



FIG. 1



FIG. 2



FIG. 3



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6




Fig. 7



Fig. 8

FIBER OPTIC MEDIA CONVERTERS

ITEM #	DESCRIPTION	FIG.
NAP-6000	ETHERNET TP TO ST FIBER MEDIA BRIDGE "IEEE 802.3. IEEE 802.3u, 10/100 BASE-TX" 100 BASE-FX - RJ-45 AND ST CONNECTORS FULL/HALF DUPLEX SELECTABLE	1
NAP-6001	ETHERNET TP TO SC FIBER MEDIA BRIDGE "IEEE 802.3. IEEE 802.3u, 10/100 BASE-TX" 100 BASE-FX - RJ-45 AND SC CONNECTORS FULL/HALF DUPLEX SELECTABLE	2

FIBER OPTIC TOOLS

ITEM #	DESCRIPTION	FIG.
TFS-1200	FIBER KEVLAR SCISSORS • NON-SLIP SERRATED BLADES • HIGH-LEVERAGE - QUICK ACTION • SHEER CUTS WITH EASE	3
TFS-1300	FIBER OPTIC STRIPPING TOOL • STRIPS OUTER JACKET • STRIPS INSULATION .010-.0125 • CUTS FIBER • ROTARY FUNCTION	4

4-WAY UTP STRIPPING TOOL

ITEM #	DESCRIPTION	FIG.
TEL-6105	4-WAY STRIPPING TOOL-CUTS FLAT AND ROUND TELEPHONE & UTP CABLE-STRIPS FLAT SILVER SATIN TELEPHONE CABLE AND UTP CABLE WITH O.D. ADJUSTMENT SCREW	5

CABLE SLITTER

ITEM #	DESCRIPTION	FIG.
TCS-1100	ADJUSTABLE CABLE SLITTER FOR CABLE O.D. 1/8" TO 1.0" DIA. ADJUSTABLE BLADE DEPTH NEW ERGONOMIC ABS HANDLE DESIGN	6

PALM SAVER TERMINATION AID

ITEM #	DESCRIPTION	FIG.
TEL-4000	PALM SAVER TERMINATION AID FOR TERMINATING KEYSTONE JACKS	7

PALM SAVER TERMINATION AID

ITEM #	DESCRIPTION	FIG.
GMP-1000	10 PIECE ALLIGATOR JUMPERS 20 AWG	8