

PRODUCT FINDER



Making Technology Work

Search our website...

Quest part no. search

Home

> [Store](#) > [Accessories](#) > [All](#) > [Non-Hinged Wall Mount Extended Bracket Products](#)

Non-Hinged Wall Mount Extended Bracket


Marketing

Technical Support

What's New

About Us

Contact Us



[Click to Enlarge](#)



Rack Size Height (Rack Units)	3.5" (2U)
	5.25" (3U)
	7.0" (4U)
	10.5" (6U)
Rack Size Width	21"
Rack Size Depth	7" or 12"
Mounting Format	19"
Hinged Swing Out Design	No
Dual Tapped Rails	Yes (#12-24)
Electrostatic Powdercoat MicroFinish	Black
Screws & Washers (#12-24)	4 each
Compliance	EIA-310D
Delivery Style	Assembled

[Pin it](#)

[Tweet](#)

[Items](#) [Description](#) [Features](#) [Spec Sheets](#)

SKU	Ship Weight	Color	Ext. Dimensions	Inches	Rack Units	UPC
WB19-0412N	9.5 lbs.	Black	21"wx 12"d	7"	4U	80011802079
WB19-0612N	11 lbs.	Black	21"wx 12"d	11"	6U	80011802082
WB19-0712N	11 lbs.	Black	21"wx 12"d	12"	7U	80011802117

Related Items:

[Horizontal PDU Surge Strip, 12 Front 120VAC/15A EM/RFI Outlets with 6ft Swiveling Power Cord](#)



[» details](#)

[#12-24 Phillips Head Mounting Screws](#)



[» details](#)

[Horizontal Cable Manager](#)



[» details](#)

- QUEST SELECT**
- QUEST TECHNOLOGY INT'L
 - QUEST MANUFACTURING
 - QUEST FACTORY OUTLET
 - LOCJACK
 - PREMIERE RACEWAY



AFFILIATIONS

Customer Service

- » [Contact Us](#)
- » [Sales Support](#)
- » [Custom Requests](#)
- » [Help/FAQ's](#)
- » [Distributor Finder](#)

Technical Support

- » [Training Resources](#)
- » [Cross Reference](#)
- » [How-To Video's](#)
- » [Installation Instructions](#)
- » [Product Search](#)
- » [Industry Resources](#)

Marketing

- » [New Products](#)
- » [Press Releases](#)
- » [Product Literature](#)
- » [Catalog Downloads](#)
- » [Trade Show Schedule](#)
- » [Close-Out Specials](#)

Company Information

- » [Company Contacts](#)
- » [About Quest](#)
- » [Warranty Information](#)
- » [Certifications](#)
- » [Company Affiliations](#)

[Join Our Mailing List](#)

Social Media



Copyright 2014, Quest Manufacturing. All Rights Reserved. | [Terms of Service](#) | [Privacy Policy](#) | [Sitemap](#) | [Website: www.14east.com](#)