




Supplement Product Catalog Q502



QUEST's Enhanced Category 5e/350Mhz UTP patch cords feature slim design molded strain-relief boots in both snagless and non-snagless types. They exceed specified performance as stated in TIA/EIA 568-A for connecting hardware and are manufactured using 350Mhz cable with 50u"gold plated modular connectors. Available in 568B and crossover wiring configurations. Offered in 7 colors for easy port or link identification. Lifetime warranted.

non-snagless

COLOR	3 FT		FT 15 FT	25 FT	
					NIDO 040E
BLACK	NPC-0103	NPC-0107	NOC-0110		NPC-0125
BLUE	NPC-0203		NPC-0210	NPC-0215	NPC-0225
GRAY	NPC-0903		NPC-0910	NPC-0915	NPC-0925
GREEN	NPC-0603	NPC-0607	NPC-0610	NPC-0615	NPC-0625
RED	NPC-0303	NPC-0307	NPC-0310	NPC-0315	NPC-0325
WHITE	NPC-0803	NPC-0807	NPC-0810	NPC-0815	NPC-0825
YELLOW	NPC-0503	NPC-0507	NPC-0510	NPC-0515	NPC-0525
		SNF	GLESS		
COLOR	1 FT	3 FT	5 FT	7 FT	10 FT
BLACK	NPC-1101	NPC-1103	NPC-1105	NPC-1107	NPC-1110
BLUE	NPC-1201	NPC-1203	NPC-1205	NPC-1207	NPC-1210
GRAY	NPC-1901	NPC-1903	NPC-1905	NPC-1907	NPC-1910
GREEN	NPC-1601	NPC-1603	NPC-1605	NPC-1607	NPC-1610
RED	NPC-1301	NPC-1303	NPC-1305	NPC-1307	NPC-1310
WHITE	NPC-1801	NPC-1803	NPC-1805	NPC-1807	NPC-1810
YELLOW	NPC-1501	NPC-1503	NPC-1505	NPC-1507	NPC-1510
COLOR	15 FT	25 FT	50 FT	100 FT	
BLACK	NPC-1115	NPC-1125	NPC-1150	NPC-1100	
BLUE	NPC-1215	NPC-1225	NPC-1250	NPC-1200	
GRAY	NPC-1915	NPC-1925	NPC-1950	NPC-1900	
GREEN	NPC-1615	NPC-1625	NPC-1650	NPC-1600	
RED	NPC-1315	NPC-1325	NPC-1350	NPC-1300	
WHITE	NPC-1815	NPC-1825	NPC-1850	NPC-1800	
YELLOW	NPC-1515	NPC-1525	NPC-1550	NPC-1500	
		CBC	550VER		
COLOR	3 FT		7 FT 10		25 FT
RED	NPC-2303	NPC-2305 NP(	C-2307 NPC-2	2310 NPC-2315	5 NPC-2325
YELLOW	NPC-2503	NPC-2505 NPC	C-2507 NPC-2	2510 NPC-2515	5 NPC-2525


# **CUSTOM LENGTHS AVAILABLE**



Fig. 3

Newly offered are Din type cable assemblies, which are configured and used, for a variety of computer connecting applications. Among them are Keyboard or Mouse extension cables for AT and PS2 types and also for MIDI (Music Instrument Digital Device) applications. These are quality cables, which are molded and constructed with shielded cable. Also available are Mini-Din in-line adapters.






Please see Quest Full Line Catalog #Q700 for complete interconnect products

NCC-3906 MINI DIN 6 FEMALE-FEMALE INLINE COUPLE


DESCRIPTION

ITEM #









In addition to our line of computer cables found in our master catalog, Quest is adding specialty application cables. These include null-modem, HP plotter and VGA cables. Also included are new lengths for the IEEE printer cable series.

## FEATURES: (Except VGA cables)

- ALUMINUM MYLAR SHIELD
- TINNED COPPER DRAIN WIRE
- TINNED STRANDED COPPER CONDUCTORS
- MOLDED WITH THUMBSCREWS
- PVC JACKET
- LIFETIME WARRANTY

#### IEEE PRINTER CABLES

TEM #	DESCRIPTION	_16
NCC-4006	6' IEEE D25 MALE TO 36P CENTRONICS PRINTER CABLE	1
NCC-4010	10' IEEE D25 MALE TO 36P CENTRONICS PRINTER CABLE	1
NICC 400E	OE, IEEE DOE VVVI E TO OCD CEVILDOVICE DDIVILED CVDI E	. 1

#### HP PLOTTER CABLES

ITEM #	DESCRIPTION	FIE.
NCC-5306	6' D9 FEMALE TO D25 MALE HP PLOTTER CABLE	2
NCC-5310	10' D9 FEMALE TO D25 MALE HP PLOTTER CABLE	2

# NULL MODEM CABLES

NCC-6106	6' NULL MODEM D25 MALE TO D25 FEMALE	4
NCC-6110	10' NULL MODEM D25 MALE TO D25 FEMALE	4
NCC-6206	6' NULL MODEM D25 MALE TO D25 MALE	3
NCC-6210	10' NULL MODEM D25 MALE TO D25 MALE	3
	VGA CABLES	)

ITEM #	DESCRIPTION

NCC-9106	6' HD15 MALETO 5 BNC VGA CABLE	5
NCC-9115	15' HD15 MALE TO 5 BNC VGA CABLE	5

Please see Quest Full Line Catalog #Q700 for complete interconnect products







Fig. 5

Quest now offers an array of external SCSI (Small Computer System Interface) cables that allows the attachment of various external devices to a single controller card in a computer. SCSI is often used in high-end PC's and server computers because of its greater flexibility and faster performance when compared to other Input/Output (I/O) technologies. SCSI I specifies DB25, DB50 or Centronics 36 connectors. SCSI II specifies Half Pitch DB50 and SCSI III specifies Half Pitch DB68 connectors.

## FEATURES :

- ALUMINUM MYLAR SHIELD
- TINNED COPPER DRAIN WIRE
- TINNED STRANDED COPPER CONDUCTORS
- MOLDED WITH THUMBSCREWS
- PVC JACKET
- LIFETIME WARRANTY

#### VGA CABLES

ITEM #	DESCRIPTION	-IG.
NCC-8006	6' CENT. 50 MALE TO CENT. 50 MALE	1
NCC-8010	10' CENT. 50 MALE TO CENT. 50 MALE	1
NCC-8506	6' SCSI II H.P. DB50 MALE TO SCSI II H.P. DB50 MALE	2
NCC-8510	10' SCSI II H.P. DB50 MALE TO SCAI II H.P. DB50 MALE	2
NCC-8206	6' SCSI II H.P. DB50 MALE TO SCSI I CENT. 50 MALE	3
NCC-8210	10' SCSI H.P. DB50 MALE TO SCSI I CENT. 50 MALE	3
NCC-8303	3' SCSI II H.P. DB50 MALE TO SCSI I DB25 MALE	4
NCC-8306	6' SCSI II H.P. DB50 MALE TO SCSI I DB25 MALE	4
NCC-8310	10' SCSI II H.P. DB50 MALE TO SCSI I DB25 MALE	4
NCC-8406	6' SCSI III H.P. 68 MALE TO SCSI III H.P. 68 MALE	5
NCC-8410	10' SCSI III H.P. 68 MALE TO SCSI III H.P. 68 MALE	5

Please see Quest Full Line Catalog #Q700 for complete interconnect products








Fig. 2





