



RAF ELECTRONIC
HARDWARE

a Division of MW Industries, Inc.



[ABOUT US](#) [WHAT'S NEW](#) [CONTACT US](#) [SERVICES](#) [QUALITY](#) [SITE MAP](#)

- [HOME](#)
- [PRODUCTS](#)
- [ONLINE CATALOG](#)
- [REQUEST QUOTE](#)
- [ORDER ONLINE](#)
- [CHECK STOCK](#)
- [REQUEST PRINT CATALOG](#)
- [REQUEST SAMPLES](#)
- [ENGINEERING DATA](#)
- [DISTRIBUTORS](#)
- [CAPABILITIES BROCHURE](#)


**CALL NOW:
203 888-2133**



NEFDA
New England Fastener
Distributor Association



1/4 Round Female Standoffs



[Home](#) [Previous](#) [Next](#)
[Related Me](#)

Ordering Code			
xxxx	xxx	x	x
	Thread		Finis
Length		Material	

PART: ????-???-??

Red ?'s show missing selections. [H](#)

Select	Part No.	Length
<input type="checkbox"/>	1678A	3/32
<input type="checkbox"/>	1678	1/8
<input type="checkbox"/>	1678T	5/32
<input type="checkbox"/>	1679	3/16
<input type="checkbox"/>	1679T	7/32
<input type="checkbox"/>	1680	1/4
<input type="checkbox"/>	1680T	9/32
<input type="checkbox"/>	1681	5/16
<input type="checkbox"/>	1681T	11/32
<input type="checkbox"/>	1682	3/8
<input type="checkbox"/>	1682T	13/32
<input type="checkbox"/>	1683	7/16
<input type="checkbox"/>	1683T	15/32
<input type="checkbox"/>	1684	1/2
<input type="checkbox"/>	1684T	17/32
<input type="checkbox"/>	1685	9/16
<input type="checkbox"/>	1685T	19/32
<input type="checkbox"/>	1686	5/8
<input type="checkbox"/>	1686T	21/32
<input type="checkbox"/>	1687	11/16
<input type="checkbox"/>	1687T	23/32
<input type="checkbox"/>	1688	3/4
<input type="checkbox"/>	1688T	25/32
<input type="checkbox"/>	1689	13/16
<input type="checkbox"/>	1689T	27/32
<input type="checkbox"/>	1690	7/8
<input type="checkbox"/>	1690T	29/32

Select	Part No.	Length
<input type="checkbox"/>	1691	15/16
<input type="checkbox"/>	1691T	31/32
<input type="checkbox"/>	1692	1"
<input type="checkbox"/>	1693	1-1/16
<input type="checkbox"/>	1694	1-1/8
<input type="checkbox"/>	1695	1-3/16
<input type="checkbox"/>	1696	1-1/4
<input type="checkbox"/>	1697	1-5/16
<input type="checkbox"/>	1698	1-3/8
<input type="checkbox"/>	1699	1-7/16
<input type="checkbox"/>	1700	1-1/2
<input type="checkbox"/>	1701	1-9/16
<input type="checkbox"/>	1702	1-5/8
<input type="checkbox"/>	1703	1-11/16
<input type="checkbox"/>	1704	1-3/4
<input type="checkbox"/>	1705	1-13/16
<input type="checkbox"/>	1706	1-7/8
<input type="checkbox"/>	1707	1-15/16
<input type="checkbox"/>	1708	2"
<input type="checkbox"/>	1709	2-1/8
<input type="checkbox"/>	1710	2-1/4
<input type="checkbox"/>	1711	2-3/8
<input type="checkbox"/>	1712	2-1/2
<input type="checkbox"/>	1713	2-5/8
<input type="checkbox"/>	1714	2-3/4
<input type="checkbox"/>	1715	2-7/8
<input type="checkbox"/>	1716	3"

Select	Part No.	Length
<input type="checkbox"/>	1717	3-1/4
<input type="checkbox"/>	1718	3-1/2
<input type="checkbox"/>	1719	3-3/4
<input type="checkbox"/>	1720	4"
<input type="checkbox"/>	1721	4-1/4
<input type="checkbox"/>	1722	4-1/2
<input type="checkbox"/>	1723	4-3/4
<input type="checkbox"/>	1724	5"
<input type="checkbox"/>	1725	5-1/4
<input type="checkbox"/>	1726	5-1/2
<input type="checkbox"/>	1727	5-3/4
<input type="checkbox"/>	1728	6"
<input type="checkbox"/>	1729	6-1/4
<input type="checkbox"/>	1730	6-1/2
<input type="checkbox"/>	1731	6-3/4
<input type="checkbox"/>	1732	7"
<input type="checkbox"/>	1733	7-1/4
<input type="checkbox"/>	1734	7-1/2
<input type="checkbox"/>	1735	7-3/4
<input type="checkbox"/>	1736	8"
<input type="checkbox"/>	1737	8-1/4
<input type="checkbox"/>	1738	8-1/2
<input type="checkbox"/>	1739	8-3/4
<input type="checkbox"/>	1740	9"
<input type="checkbox"/>	1741	9-1/4
<input type="checkbox"/>	1742	9-1/2
<input type="checkbox"/>	1743	9-3/4
<input type="checkbox"/>	1744	10"

Select	Code	Thread
<input type="checkbox"/>	440	4-40
<input type="checkbox"/>	632	6-32
<input type="checkbox"/>	832	8-32
<input type="checkbox"/>	1032	10-32

[Thread depth information](#)

Select	Code	Material	RoHS
<input type="checkbox"/>	AL	Aluminum	YES
<input type="checkbox"/>	B	Brass	YES
<input type="checkbox"/>	SS	Stainless Steel	YES
<input type="checkbox"/>	S	Steel	YES
<input type="checkbox"/>	N	Nylon	YES
<input type="checkbox"/>	PH	Phenolic	YES

[Material Specifications](#)

SELECT FINISH:

select a material first

* Finishes ending with an asterisk are not RoHS Compliant

[Ordering non-standard items](#)