




MW Industries, Inc.

- Home
- Products
- Online Catalog
- Request Quote
- Order Online
- Check Stock
- Request Print Catalog
- Request Samples
- Engineering Data
- Distributors
- Capabilities Brochure

Home > **Style 1 Ferrules for Handles**

**STYLE 1 FERRULES FOR HANDLES**



[Home](#) [Next](#)

Ordering Code		
xxx	xx	x
Part Number	Material	Finish

**PART: 8976 SS 26**

Red ?'s show missing selections. [Help](#)

- [Material Specifications](#)
- [Ordering non-standard items](#)
- [Request a Drawing](#)

**Add to Cart**

CALL NOW:  
203 888-2133

Qty1 \*

Qty2

Qty3



Part Number \*

Select	Part No.	A+.005-.005	B+.005-.005	C+.005-.005	D+.005-.005	E+.005-.005	F+.015-.015
<input type="radio"/>	972	1/4	.046	.125	.116	.136	13/64
<input type="radio"/>	8973	1/4	.046	.125	.116	.161	13/64
<input type="radio"/>	8974	5/16	.062	.125	.141	.203	17/64
<input type="radio"/>	8975	3/8	.062	.125	.141	.260	5/16
<input checked="" type="radio"/>	8976	3/8	.062	.187	.204	.260	5/16
<input type="radio"/>	8977	7/16	.062	.187	.204	.260	5/16
<input type="radio"/>	8978	1/2	.062	.250	.187	.260	11/32
<input type="radio"/>	8979	15/32	.062	.250	.221	.320	13/32
<input type="radio"/>	8980	9/16	.062	.250	.221	.320	13/32
<input type="radio"/>	8981	5/8	.093	.375	.250	.385	15/32
<input type="radio"/>	8982	3/4	.093	.375	.250	.385	15/32

Material \*

Select	Code	Material	RoHS
<input type="radio"/>	AL	Aluminum	YES
<input type="radio"/>	B	Brass	YES
<input checked="" type="radio"/>	SS	Stainless Steel	YES
<input type="radio"/>	S	Steel	YES

<input type="radio"/>	19-Caustic etch
<input type="radio"/>	20-Passivation
<input type="radio"/>	21-Dark grey anodize
<input type="radio"/>	22-Clear anodize
<input type="radio"/>	23-Yellow green anodize
<input type="radio"/>	24-Black anodize
<input type="radio"/>	25-Black oxide brass
<input checked="" type="radio"/>	26-Black oxide SS
<input type="radio"/>	27-Electro tin solder 60/40*
<input type="radio"/>	28-Zinc yellow chromate
<input type="radio"/>	29-Brushed
<input type="radio"/>	34-Satin clear anodize
<input type="radio"/>	35-Satin black anodize