



DR-25-TW-1-1/2-0-SP Product Details

[Share](#) [Print](#) [Email](#)


Active

Heat Shrink Tubing

DR-25-TW-1-1/2-0-SP

DR-25-TW-1-1/2-0-SP

TE Internal Number: 8895704002

Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = DR-25
- Product Source = U.S.
- Very Flexible
- Thin Wall Style

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Heat Shrinkable Tubing
Color	Black

Dimensions

Expanded ID, Min. (mm [in])	38.00 [1.496]
Recovered ID, Max. (mm [in])	19.10 [0.752]

Body Features

Product Name	DR-25
Pliancy	Very Flexible
Wall Style	Thin
Wall Type	Single
Material	Crosslinked Elastomer
Shrink Ratio	2:1

Fluid Type	Aviation Fuel, Brake Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Water
------------	--

Resistant To	Abrasion, Fluids, Mechanical Damage
--------------	-------------------------------------

Wall Thickness - Full Recovery (Nominal) (mm [in])	1.02 [0.040]
--	--------------

Housing Features

Material Systems	Yes
Material Systems Code	25

Industry Standards

Government/Industry Qualification	No
Flammability Rating	Flame-Retardant
UL Rating	None
CSA Certified	No

Approved Standards	BS 4G 198 Part 3 Type 10A, DEF Std 59-97 Issue 3 Type 6B, RK-6008/2, SAE AMS-DTL-23053/16, VDE 0341 Part 9005 Type A, VG95343 Part 5D Type D
--------------------	--

RoHS/ELV Compliance	RoHS compliant, ELV compliant
---------------------	-------------------------------

Lead Free Solder Processes	Not relevant for lead free process
----------------------------	------------------------------------

RoHS/ELV Compliance History	Always was RoHS compliant
-----------------------------	---------------------------

Environmental

Fluid Resistance	Splash Protection
Operating Temperature (°C)	-75 - +150

Conditions for Usage

Full Recovery Temperature (°C)	175
Shrink Temperature, Min. (°C)	150
High Temperature Compatible	Yes

Operation/Application

Emission Free	No
Product Use	Cables, Harnesses
Application	Aerospace, Harness Protection, Insulation and Protection, Military

Packaging Features

Packaging Method	Spool
------------------	-------

Product Availability

Product Source	U.S.
----------------	------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

