




202D211-4-09-0 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Molded Parts

202D211-4-09-0

202D211-4-09-0 ✔

TE Internal Number: CR3014-000

Product Highlights [View All](#)

- SAE AS81765/1 Type II
- Molded Part Type = Molded Boot
- Molded Part Lip = With Lip
- Operating Temperature = -55 - 135 °C
- Adhesive Options = None

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

| Product Type Features | |
|--|-------------------------------|
| Molded Part Type [?] | Molded Boot |
| Molded Part Lip | With Lip |
| Angle | 180° |
| Adhesive Description | Adhesive Purchased Separately |
| Size | 11 |
| Family Name | 202D2 |
| Color | Black |
| Mechanical Attachment | |
| Adhesive Pre-Coating | Without |
| Dimensions | |
| Expanded ID, Min. (mm [in]) | 22.40 [0.880] |
| Recovered ID, Max. (mm [in]) | 11.40 [0.450] |
| Body Features | |
| Material | Polyolefin Flexible Modified |
| Housing Features | |
| Material Systems Code [?] | 10 |
| Max. Inside Diameter of Part (mm [in]) | 11.40 [0.450] |

| Configuration Features | |
|---|------------------------------------|
| Material Code | 4 |
| Industry Standards | |
| Government/Industry Qualification | No |
| Approved Standards | SAE AS81765/1 Type II |
| RoHS/ELV Compliance [?] | RoHS compliant, ELV compliant |
| Lead Free Solder Processes [?] | Not relevant for lead free process |
| RoHS/ELV Compliance History | Always was RoHS compliant |
| Environmental | |
| Operating Temperature (°C) | -55 - +135 |
| Operation/Application | |
| Application | General Purpose |
| Purchasing Information | |
| Adhesive Code | S1017, S1048 |
| Other | |
| Adhesive Options | None |
| Brand | Raychem |

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

