

SEARCH

CART

Products ▼ Catalogs Free Samples Free CAD Knowledge Center Contact Us

Home > PCB & Electronics Hardware > Supports > Standard Snap Lock Supports



**PCB Sprt, Top HI: Lock Arrow .125 in/ .030 in-.078 in Pnl, Bottom HI: Lock Arrow .125 in/.030 in-.078 in, Nat, UL94 V-2 Nylon 6/6**

● In Stock

Item Code: DLCBSM-8-01

DLCBSM-8-01 has a Locking Arrowhead for a .125 in (3.2 mm) hole in a .078 in (2 mm) panel on one side and a Locking Arrowhead in a .078 in (2 mm) panel on the opposite side. The spacer length is .500 in (12.7 mm)



Description	Quantity	Options
Spacer Length	: .500 in (12.7 mm)	<input type="text" value="1000"/>
Hole A Fix Type	: Locking Arrowhead	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
Hole B Fix Type	: Locking Arrowhead	
Hole Diameter A	: .125 in (3.2 mm)	
Hole Diameter B	: .125 in (3.2 mm)	
Locking Head Height A	: .16 in (4.1 mm)	
Locking Head Height B	: .16 in (4.1 mm)	
Body Diameter	: .17 in (4.3 mm)	
Full Material	: Nylon 6/6	
Color	: Natural	
Operating Temperature Range	: -40 - 185 °F (-40 - 85 °C)	
Material Flammability Standard	: UL94 V-2	
Style	: 6	
Brand	: Richco	
Material	: Nylon	
Panel Thickness A Range	: .030 - .078 in (0.8 - 2 mm)	
Panel Thickness B Range	: .030 - .078 in (0.8 - 2 mm)	

Downloads ▼

Print Page

Recently Viewed



PCB Sprt, Top HI: Lock Arrow .125 in/ .030 in-.078 in Pnl, Bottom HI: Lock Arrow .125 in/.030 in-.078 in, Nat, UL94 V-2 Nylon 6/6

ESSENTIAL SOLUTIONS DELIVERED

Abrasives & Grinding  
Access Hardware  
Adhesives, Sealants & Tapes  
Bearings & Power Transmissions

Clamps & Workholdings  
Cutting & Machining  
Extrusions & Structural Systems  
Fasteners

Fiber, Wire & Cable Management  
Flange Protection  
Knobs, Handles & Grips  
Material Handling

PCB & Electronics Hardware  
Pneumatics & Hydraulics  
Raw Materials  
Tamper Evident & Security Seals



**About Us**

- About Essentra Components
- About Essentra PLC
- Locations
- Knowledge Center

**Customer Service**

- Contact Us
- Catalogs
- Sample Program
- Free CAD
- Careers
- Distributor Portal

**Policies**

- Privacy Policy
- Terms and Conditions of Sale
- Terms and Conditions of Purchase
- Environmental Policy
- Health and Safety
- Quality Statement

**Terms of Use**

- Website Terms of Use
- Cookie Policy

**ABOUT SSL CERTIFICATES**