


# 222K132-25/42-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

## Molded Parts

222K132-25/42-0

**222K132-25/42-0**

TE Internal Number: 632965-000

### Product Highlights [View All](#)

- VG95343 Parts 6,7,8 and 9
- Molded Part Type = Molded Boot
- Molded Part Shape = 90°
- Molded Part Lip = With Lip
- Operating Temperature = -20 - 60 °C

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Documents](#) | [Features](#) | [Compliance](#)

### Related Products

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

**Please Note:**  
 Use the Product Drawing for all design activity

Product Type Features	
Molded Part Type	Molded Boot
Molded Part Shape	90°
Molded Part Lip	With Lip
Angle	90°
Adhesive Description	General Purpose Pre-Coat Adhesive
Size	32
Family Name	222K1
Color	Black

Mechanical Attachment	
Adhesive Pre-Coating	With

Dimensions	
Cable Diameter Range (mm [in])	14.20 - 30.00 [0.560 - 1.180]
Expanded ID, Min. (mm [in])	30.00 [1.180]
Recovered ID, Max. (mm [in])	14.30 [0.560]

Body Features	
Material	Fluid Resistant Modified Elastomer

Housing Features	
Material Systems Code	25
Max. Inside Diameter of Part (mm [in])	14.30 [0.560]

Configuration Features	
Material Code	25

Industry Standards	
Government/Industry Qualification	No
Approved Standards	VG95343 Parts 6,7,8 and 9
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental	
Operating Temperature (°C)	-20 - +60

Operation/Application	
Application	General Purpose

Purchasing Information	
Adhesive Code	42

Other	
Brand	Raychem

- ### Corporate Information
- [About TE](#)
  - [Investors](#)
  - [News Room](#)
  - [Supplier Portal](#)
  - [Careers](#)
  - [Terms & Conditions](#)
  - [Privacy Policy](#)
  - [Global Accessibility Statement](#)

- ### Quick Links
- [Distributor Inventory](#)
  - [Product Cross Reference](#)
  - [Documents & Drawings](#)
  - [Product Compliance Support Center](#)
  - [Site Map](#)

- ### Customer Support
- [Email or Chat With Us](#)
  - [Find a Phone Number](#)
  - [Knowledge Base](#)
  - [Manage Your Account](#)

### Keep Me Informed