

Data sheet

E-DAT modul REG unequipped IP20 light gray

Page 1/5

P/N

1309426103-E


EAN 4250184106593

2017-06-02

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- unequipped termination unit for individual module in Modul design for mounting on TH35 rail to DIN EN 60715
- width of 1HP allows mounting up to 12 REG in standard electrical distribution panels
- when mounted as a device of protection class I, the equipotential bonding is realized directly over the top hat rail by means of an integrated equipotential spring. This has to be connected to the equipotential bonding of the building by means of a bonding terminal
- a cover protects the module against direct contact. If mounted in distributor panels with protective insulation, protection class II is guaranteed. In this case, it is necessary to remove the equipotential bonding spring.
- integrated dust protection cover (also colored)
- the following modules can be mounted: E-DAT modul, E-DAT modul coupler 180°, UAE modul, OpDAT modul LC-D and ST as well as Koax modules
- please note: not suitable for C6modul



Technical Data

General Data

Fields of application	Harsh environment
Design	Wall outlet
Color	light gray
Dimensions	
Dimension (L x W x H)	60.00 x 17.50 x 52.20 mm
Dimension (L x W x H)	2.362 x 0.689 x 2.055 in.
Horizontal pitch	1HP
Labeling option	label window with identification label
Marking option	by dust protection

Connections/interfaces

Number of ports interface 1	1
Number of ports interface 2	1
Number of equipped ports interface 1	0
Number of ports interface 2 equipped	0
Module plug-in direction	45° downwards

Mechanical characteristics

Cut-out	Modul
---------	-------

Materials and material properties

Material - Cover part(s)	Frianyl
Material - Lower housing	Frianyl
Material - Ground connection	CuSn4
Material - Dust protection	ABS
Material - Label window	ABS, transparent

Environmental conditions

Particulate ingress	IP2X
Liquid ingress/immersion	IPX0



Technical Data

Approvals

RoHS	compliant
UL listed (file no.)	DUXR.E178484

Classifications

ETIM 5.0	EC001024
ETIM 6.0	EC001024

Packing details

Type of packaging	10 pc(s) / box
Packaging unit - Weight (gram)	205.00 g
Packaging unit - Weight (pound)	0.45 lb
Packaging dimension (W x H x D)	235.00 x 165.00 x 135.00 mm
Packaging dimension (W x H x D)	9.252 x 6.496 x 5.315 in.



E-DAT modul REG unequipped IP20 light gray

P/N

1309426103-E

EAN 4250184106593

2017-06-02

Accessories

P/N	Designation
816979-0105-I	Dust protection covers for Modul patch panels subway / REG yellow
816979-0106-I	Dust protection covers for Modul patch panels subway / REG blue
816979-0107-I	Dust protection covers for Modul patch panels subway / REG green
816979-0108-I	Dust protection covers for Modul patch panels subway / REG red
899011-01	Label sheet for Modul patch panels / REG



Illustrations

Dimensional drawing

