

Search by SKU, Product Name or Keyword

**SEARCH**

**CART**

Product Information

**Contact Us**



MORE CHOICE



FREE SAMPLES



SHIPS TODAY



Home

PCB & Electronics Hardware

Spacers & Standoffs

Male To Female Standoff



**Threaded Nylon/Brass Spacer,Natural, #6-32, 1.000" Spacer**

● In Stock

**Item Code:** TN4-16-632-2

This Nylon 6/6 Round #6-32 Male To Female Insulator Standoff is 1.000 in (25.4 mm) long

Description	Quantity	Options
<b>Compatible Thread Sizes (All)</b> :#6-32	<input type="text" value="100"/>	<div style="background-color: red; color: white; text-align: center; padding: 5px; margin-bottom: 5px;"><b>Add to Cart</b></div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; text-align: center; padding: 5px;">Request Quote</div>
<b>Thread Length</b> :.250 in (6.4 mm)		
<b>Body Diameter</b> :.250 in (6.4 mm)		
<b>Spacer Length</b> :1.000 in (25.4 mm)		
<b>Full Material</b> :Nylon 6/6		
<b>Material</b> :Nylon		
<b>Material Flammability Standard</b> :UL94 V-2		
<b>Color</b> :Natural		
<b>Operating Temperature Range</b> :-40 - 185 °F (-40 - 85 °C)		
<b>Spacer Shape</b> :Round		
<b>Special Features (All)</b> :Brass Inserts		
<b>Brand</b> :Richco		
<b>Internal Thread Size Range</b> :#6-32		
<b>External Thread Size Range</b> :#6-32		

Downloads



Print Page

**Recently Viewed**



Threaded Nylon/Brass  
Spacer,Natural, #6-32,  
1.000" Spacer

Abrasives & Grinding  
 Access Hardware  
 Adhesives, Sealants & Tapes  
 Bearings & Power Transmissions  
 Caps & Plugs

Clamps & Workholdings  
 Cutting & Machining  
 Extrusions & Structural Systems  
 Fasteners  
 Feet, Casters & Glides

Fiber, Wire & Cable Management  
 Flange Protection  
 Knobs, Handles & Grips  
 Material Handling  
 Shop Supplies

PCB & Electronics Hardware  
 Pneumatics & Hydraulics  
 Raw Materials  
 Tamper Evident & Security Seals  
 Tooling & Positioning Components  
 Tools & Precision Instruments



**About Us**

About Essentra Components  
 About Essentra PLC  
 Locations  
 Knowledge Center

**Customer Service**

Contact Us  
 Catalogs  
 Sample Program  
 Free CAD  
 Careers  
 Distributor Portal

**Policies**

Privacy Policy  
 Terms and Conditions of Sale  
 Terms and Conditions of  
 Purchase  
 Environmental Policy  
 Health and Safety  
 Quality Statement

**Terms of Use**

Website Terms of Use  
 Cookie Policy

