



ESSENTRA

Search by SKU, Product Name or Keyword

SEARCH

CART



[Quick Order](#) [Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

[Home](#) > [PCB & Electronics Hardware](#) > [Supports](#) > [Standard Snap Lock Supports](#)



PCB Sprt, Top HI:Lock Arrow .118 in/ .047 in-.066 in Pnl, Bottom HI:Lock Arrow .118 in/.030 in-.078 in , Nat, UL94 V-2 Nylon 6/6

In Stock
Free sample available

Item Code: CBLS340A

CBLS340A has a Locking Arrowhead for a .118 in (3 mm) hole in a .066 in (1.7 mm) panel on one side and a Locking Arrowhead in a .078 in (2 mm) panel on the opposite side. The spacer length is .563 in (14.3 mm)



Description	Quantity	Options
Spacer Length : .563 in (14.3 mm)	<input type="text" value="1000"/>	<div style="background-color: #e91e63; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Add to Cart</div> <div style="background-color: #9e9e9e; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #9e9e9e; color: white; padding: 5px; text-align: center;">Request Quote</div>
Hole A Fix Type : Locking Arrowhead		
Hole B Fix Type : Locking Arrowhead		
Hole Diameter A : .118 in (3 mm)		
Hole Diameter B : .118 in (3 mm)		
Locking Head Height A : .11 in (2.8 mm)		
Locking Head Height B : .13 in (3.3 mm)		
Full Material : Nylon 6/6		
Color : Natural		
Operating Temperature Range : -40 - 185 °F (-40 - 85 °C)		
Material Flammability Standard : UL94 V-2		
Material Type : RMS-074		
Style : 2		
Material : Nylon		

Downloads



Print Page

Recently Viewed



PCB Sprt, Top HI:Lock Arrow .118 in/ .047 in-.066 in Pnl, Bottom HI:Lock Arrow .118 in/.030 in-.078 in , Nat, UL94 V-2 Nylon 6/6

ESSENTIAL SOLUTIONS DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components



About Us

- About Essentra Components
- About Essentra PLC
- Locations

Customer Service

- Contact Us
- Catalogs
- Sample Program
- Free CAD
- Careers
- Distributor Portal

Policies

- Privacy Policy
- Terms and Conditions of Sale
- Terms and Conditions of Purchase
- Environmental Policy
- Health and Safety
- Quality Statement

Terms of Use

- Website Terms of Use
- Cookie Policy



ABOUT SSL CERTIFICATES