



ESSENTRA

Search by SKU, Product Name or Keyword

SEARCH

CART



[Quick Order](#) [Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

Home

Fiber, Wire & Cable Manage...

Cable Ties & Mounts

Cable Tie Mounts



Cable Tie Mounts, Natural, Adhesive, 1.000 in (25.4 mm) x 1.000 in (25.4 mm)

Item Code: FTH-7A-RT-C

This 1.000 in (25.4 mm) x 1.000 in (25.4 mm) Adhesive Four Way Cable Tie Mount is made of Nylon 6/6. Cable ties up to .190 in (4.8 mm) wide can be inserted from all four sides

In Stock
Free sample available



Description	Quantity	Options
Mounting Method : Adhesive Overall Length : 1.000 in (25.4 mm) Overall Width : 1.000 in (25.4 mm) Overall Height : .28 in (7.1 mm) Hole Diameter : .170 in (4.3 mm) Compatible Screw Sizes (All) : #8 Base Material : Acrylic Based Adhesive Full Material : Nylon 6/6 Color : Natural Material Flammability Standard : UL94 V-2 UL/CSA Description : UL E71558 Style : 1 Material : Nylon;Acrylic Adhesive Compatible Cable Tie Width Range : .098 - .190 in (2.5 - 4.8 mm) Material Type : RMS-01 & RMS-15	<input type="text" value="100"/> <div style="background-color: red; color: white; padding: 5px; text-align: center; margin: 5px 0;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request Quote</div>	

Downloads



Print Page

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



About Us

[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)

Customer Service

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

Policies

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

Terms of Use

[Website Terms of Use](#)
[Cookie Policy](#)



ABOUT SSL CERTIFICATES