



Search by SKU, Product Name or Keyword



Masking Straight Cap & Plug: .172 in (4.4 mm) Cap ID, 180 °C (356 °F) Max. Temp.,.500 in (12.7 mm) Height

● In Stock
Free sample available

Item Code: SC017205B

Black EPDM Masking Straight Cap & Plug has a .172 in (4.4 mm) I.D. and Inside Height of .500 in (12.7 mm) to mask threaded or non-threaded components during finishing processes.



| Description | Quantity | Options |
|---|--|---------|
| Cap Inside Diameter : .172 in (4.4 mm) Compatible Thread Sizes (All) : #10-24 Inside Height : .500 in (12.7 mm) Material : EPDM Full Material : Ethylene Propylene Diene Monomer Rubber Color : Black Fitting Style : Push Fit Special Features (All) : Reusable Hardness : 55 ± 5 (Shore A) | <input type="text" value="1"/> <input type="button" value="Add to Cart"/> <input type="button" value="Request CAD"/> <input type="button" value="Free Sample"/> <input type="button" value="Request Quote"/> | |



Print Page

Recently Viewed



Masking Straight Cap & Plug: .172 in (4.4 mm) Cap ID, 180 °C (356 °F) Max. Temp.,.500 in (12.7 mm) Height

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments

About Us

- [About Essentra Components](#)
- [About Essentra PLC](#)
- [Locations](#)

Customer Service

- [Contact Us](#)
- [Catalogs](#)
- [Sample Program](#)
- [Free CAD](#)
- [Careers](#)
- [Distributor Portal](#)

Policies

- [Privacy Policy](#)
- [Terms and Conditions of Sale](#)
- [Terms and Conditions of Purchase](#)
- [Environmental Policy](#)
- [Health and Safety](#)
- [Quality Statement](#)

Terms of Use

- [Website Terms of Use](#)
- [Cookie Policy](#)



ABOUT SSL CERTIFICATES