



ESSENTRA

Search by SKU, Product Name or Keyword

SEARCH

CART



[Quick Order](#) [Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

[Home](#) > [Access Hardware](#) > [Panel Fasteners](#) > [Snap Latch Rivets](#)



Snap Latch Rivet: Nylon, L x H x 8.3 mm (0.327 in)W, 8.3 mm (0.327 in) Head Diameter

● In Stock
Free sample available

Item Code: SLPB-3M-B

Black Nylon Snap Latch Rivet Plunger is easily installed and removed from 5.9 - 6.1 mm (0.232 - 0.24 in) diameter holes 3.0 - 5.2 mm (0.118 - 0.205 in) thick panels.



Description	Quantity	Options
Material : Nylon	<input type="text" value="1000"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
Overall Width : 8.3 mm (0.327 in)		
Head Diameter : 8.3 mm (0.327 in)		
Head Height : 7.0 mm (0.276 in)		
Removable Panel Hole Diameter Range : 5.9 - 6.1 mm (0.232 - 0.24 in)		
Type : Plunger		
Compatible Door Thickness Range : 3.0 - 5.2 mm (0.118 - 0.205 in)		
Compatible Hole Diameter Range : 5.9 - 6.1 mm (0.232 - 0.24 in)		
Color : Black		
Compatible Part Numbers (All) : SLG-3M-B		
Compatible Panel Thickness Range : 5.2 mm (0.205 in)		
Compatible Hole Diameter : 6.1 mm (0.24 in)		
Rivet Type : Snap Latch		
Full Material : Nylon 6		

Downloads



Print Page

Recently Viewed



Snap Latch Rivet: Nylon,
L x H x 8.3 mm (0.327
in)W, 8.3 mm (0.327 in)
Head Diameter

ESSENTIAL SOLUTIONS

DELIVERED

[Abrasives & Grinding](#)
[Access Hardware](#)
[Adhesives, Sealants & Tapes](#)
[Bearings & Power Transmissions](#)
[Caps & Plugs](#)

[Clamps & Workholdings](#)
[Cutting & Machining](#)
[Extrusions & Structural Systems](#)
[Fasteners](#)
[Feet, Casters & Glides](#)

[Fiber, Wire & Cable Management](#)
[Flange Protection](#)
[Knobs, Handles & Grips](#)
[Material Handling](#)
[Shop Supplies](#)

[PCB & Electronics Hardware](#)
[Pneumatics & Hydraulics](#)
[Raw Materials](#)
[Tamper Evident & Security Seals](#)
[Tooling & Positioning Components](#)
[Tools & Precision Instruments](#)



About Us

- About Essentra Components
- About Essentra PLC
- Locations

Customer Service

- Contact Us
- Catalogs
- Sample Program
- Free CAD
- Careers
- Distributor Portal

Policies

- Privacy Policy
- Terms and Conditions of Sale
- Terms and Conditions of Purchase
- Environmental Policy
- Health and Safety
- Quality Statement

Terms of Use

- Website Terms of Use
- Cookie Policy



ABOUT SSL CERTIFICATES