

NPB 574

Switchcraft®

StudioPatch® Series DB25 Breakout Cable & Audio Snakes

Audio Snake Part Numbers:

- RCA10TS
(RCA to 1/4" TS)
- RCA10RCA
(RCA to RCA)
- RCA10RCAB
(RCA to RCA - black
handle / gold plated
contacts)
- TRSF10XLRM
(1/4" TRS Female to XLR
Male)
- XLRM10XLRF
(XLR Male to XLR Female)
- XLRM10XLRFB
(XLR Male to XLR Female -
black handle / gold plated
contacts)
- TS10TS
(1/4" TS to 1/4" TS)
- TRS10TRS
(1/4" TRS to 1/4" TRS)
- XLRF10TRS
(XLR Female to 1/4" TRS)
- XLRM10TRS
(XLR Male to 1/4" TRS)

*Above part numbers
come standard as 10'.
5' versions also available
by replacing 10 in the part
number with 05. Custom
lengths also available.



StudioPatch® Series Audio Snakes and DB25 Breakout Cables are designed for high quality, professional audio and broadcast systems. They are a perfect cabling solution for audio interfaces, audio consoles, audio patchbays, stage boxes, or any other application where analog or digital audio equipment is used.

Each cable is built by hand at our Chicago, IL manufacturing facility using premium Switchcraft® AAA XLR connectors, Switchcraft® 280, 297, and 131 1/4" jacks and plugs, Switchcraft® 3502A Series RCA plugs, AMP DB25 connectors, and Belden®110 Ohm eight-pair cabling.

For more information, visit:

http://www.switchcraft.com/products/pdf_files/db25.pdf

Switchcraft®
www.switchcraft.com
5555 N. Elston Avenue/Chicago, IL 60630
Phone: 773-792-2700 Fax: 773-792-2129

DB25 Breakout
Part Numbers:

-DB25M10XLRM
(DB25 to 8-XLR MALE)

-DB25M10XLRF
(DB25 to 8-XLR FEMALE)

-DB25M10XLRMXMLRF
(DB25 to 4-XLR MALE
and 4-XLR FEMALE)

-DB25M10TRS
(DB25 to 8-1/4" TRS)

-DB25M10DB25M
(DB25 to DB25)

-DB25M10DB25MAES
(DB25 to DB25 AES/EBU
CROSS-WIRED PINOUT)

-DB25MM10TRS
(2 x DB25 to 8-1/4" TRS)
(For connecting unbalanced
1/4" TRS console insert
points to a patchbay with
DB25 connections on the
back).

*Above part numbers
come standard as 10'.
2' and 3' versions also
available by replacing
10 in the part number
with 02 or 03. Custom
lengths also available.

DB25M10TRS



DB25M10XLRM



DB25MM10TRS

