



SCHROFF

Project - 0 item(s)

MY PROJECT LIST


- PRODUCTS**
- APPLICATIONS**
- INDUSTRIES**
- NEW PRODUCTS**
- CONFIGURATORS**
- Products ▾
- Search
-

Home > Front handle, one-piece, width 12.2 mm, clear anodised



Front handle, one-piece, width 12.2 mm, clear anodised

SCHROFF



Catalog Number: 10501-007

[Back To Product](#)

- Static load-carrying capacity 30 kg/pair
- Bolted from rear

Product family:

- RatiopacPRO
- PropacPRO
- CompacPRO
- Comptec
- EuropacPRO

Note:

Please order assembly part kit separately.

Accessory category:

Mechanical Accessories

Accessory type:

Front panel

Individual Component Type:

Handle

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



Select product specifications before modifying or adding to project list or requesting a quote.

Height-U-defining

Height-mm-defining

Color-Surface-defining

Type-defining

[Clear Selection](#)

Quantity

Add Item to Project List +

Links

- Main Catalog - Desk-top cases accessories
- Main Catalog - EuropacPRO
- Native CAD files


Technical Data

Type	Straight version
Application	For 5 U 19"-Frontpanel, rack mount cases
Delivery is exclusively made in Standard Pack Quantity (SPQ)	10
Color/Surface	anodised
Dimension A mm	194.0
Dimension E mm	180.0

Delivery Comprises:

Item	Quantity	Description
1	1	Front handle, anodised aluminium extrusion

Accessories



Panhead screw, cross recess (M5x12), steel zinc plated, for 19" front panel, PU 100 pcs

21100-788

[Add Item to Project List +](#)

EXPLORE

- [About Us](#)
- [Services & Capabilities](#)
- [News & Events](#)
- [Newsletter Subscriptions](#)
- [Strategic Partnerships](#)
- [Investor Relations](#)

CONTACT

- [Customer Service](#)
- [Find a Sales Office or Distributor](#)
- [Global Locations](#)
- [Product Compliance & Certifications](#)
- [Partner Login](#)

DOWNLOAD

- [Download Center](#)
- [Reference Projects](#)
- [Videos](#)
- [Product Configurators](#)
- [Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

