

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

<b>Extended Product Type:</b>	BJMI8-5
<b>Product ID:</b>	1SNA176672R0100
<b>EAN:</b>	3472591766721
<b>Catalog Description:</b>	BJMI8-5 POLES Jumper Bars
<b>Long Description:</b>	- IP20 assembled screw jumper bars, - Fractionnable model with captive screws and spacers, - Allows connection between consecutive blocks only.

## Ordering

<b>Color:</b>	Grey
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-J Accessories
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-J Accessories

## Dimensions

<b>Product Net Width:</b>	8 mm
<b>Product Net Height:</b>	23.3 mm
<b>Product Net Depth / Length:</b>	8 mm
<b>Product Net Weight:</b>	12.2 g

## Technical

<b>Spacing:</b>	8 mm
<b>Function:</b>	Jumper Bars
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 41 A
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

**Suitable For:** C6/8  
D2.5/8.ADO  
D2.5/8.ADO.NF  
D4/8.ADO  
D4/8.ADO.NF  
D6/8.ADO  
D6/8.ADO.NC  
D6/8.ADO.RS  
D6/8.D2.ADO  
M4/8.D2.SB  
M4/8.D2.SF  
M6/8  
M6/8.D  
M6/8.D2.NC  
M6/8.NC  
M6/8.RS

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225001C1009
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-J Accessories
<b>RoHS Information:</b>	1SND230492F0201

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 6:</b>	EC000489 - Cross-connector for terminal block

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	155 mm
<b>Package Level 1 Depth / Length:</b>	200 mm
<b>Package Level 1 Height:</b>	5 mm
<b>Package Level 1 Gross Weight:</b>	0.122 kg
<b>Package Level 1 EAN:</b>	3472591766721
<b>Package Level 2 Units:</b>	500 piece
<b>Product Packing Type:</b>	Bag

