



Search by part # or keyword

Products

Industries & Solutions

Resources

TE Store

Sign In



CC-38-50-SN-M12-DOUB

CC38-50-SN-M12-DOUB



Raychem | Raychem CC

TE Internal #: **EF8412-000**

TE Internal Description: **CC38-50-SN-M12-DOUB**

[All TE'S RAYCHEM CABLE CLEATS \(75\)](#)

Product Availability : **AMERICAS, ANZPAC, ASIA, China, EMEA**

Number of Cables to be Mounted : **2**

Minimum Cable Diameter : **38 mm [1.48 in]**

Maximum Cable Diameter : **50 mm [1.95 in]**

Bolt Hole Centers : **75 mm [2.93 in]**

[Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Product Description

TE's Raychem cable cleats are advanced cable tightening systems for low, medium and high voltage applications.

[View All TE'S RAYCHEM CABLE CLEATS \(75\)](#)

Product Drawings

CC38-50-SN-M12-DOUB

[CC38-50-SN-M12-DOUB](#) English

Datasheets & Catalog Pages

TE's RAYCHEM CABLE CLEATS

[ENG_DS_EPP-2211_1812.pdf](#) English

Product Description

TE's Raychem cable cleats are advanced cable tightening systems for low, medium and high voltage applications.

[View All TE'S RAYCHEM CABLE CLEATS \(75\)](#)

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Bolt (mm): **M12**

Type : **Cable Clamp**



hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?

HARDWARE, GROUNDING & MOUNTING
CC-38-50-SN-M12-DOUB
 CC38-50-SN-M12-DOUB



Non-Stocked

Product Availability : **AMERICAS, ANZPAC, ASIA, China, EMEA**
 Number of Cables to be Mounted : **2**
 Minimum Cable Diameter : **38 mm**
 Maximum Cable Diameter : **50 mm**

HARDWARE, GROUNDING & MOUNTING
CC-38-50-PL-M12-DOUB
 CC38-50-PL-M12-DOUB



Non-Stocked

Product Availability : **AMERICAS, ANZPAC, ASIA, China, EMEA**
 Number of Cables to be Mounted : **2**
 Minimum Cable Diameter : **38 mm**
 Maximum Cable Diameter : **50 mm**

HARDWARE, GROUNDING & MOUNTING
EF3981-000
 CC38-50-SN-M12



Non-Stocked

Product Availability : **AMERICAS, ANZPAC, ASIA, China, EMEA**
 Number of Cables to be Mounted : **1**
 Minimum Cable Diameter : **38 mm**
 Maximum Cable Diameter : **50 mm**

HARDWARE, GROUNDING & MOUNTING
EF3980-000
 CC38-50-PL-M12



Non-Stocked

Product Availability : **AMERICAS, ANZPAC, ASIA, China, EMEA**
 Number of Cables to be Mounted : **1**
 Minimum Cable Diameter : **38 mm**
 Maximum Cable Diameter : **50 mm**

Also in the Series | [Raychem CC](#)



Hardware, Grounding
& Mounting (52)

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)