



Representative

Catalog Number: PAA400
Product ID: 7TAA267200R0016
UPC Number: 78378633005
EAN Number: 05415022349108
Status: A

Aluminum Type PAA - Two Bolt Aluminum Parallel Groove Clamp for Wire Range Main: 336.4-1/0, 1/0-6 AR ASCR 400-1/0 Str., 1/0-6 AR AL/CU, Tap: 336.4-1/0 ASCR 400-1/0 Str. ALCU

- Galvanized Steel Carriage Bolt, Nut and Lockwasher included

North American Specifications (UNSPSC)

| | |
|--------------------------|---|
| UNSPSC | 39121449 Wire or cable compression splice |
| IGCC | 4669 Wire or cable compression splice |
| Brand Name | Blackburn |
| Type | Parallel-Groove Clamp |
| Special Features | High-Strength, Heat-Treated Cast Aluminum Alloy provides Secure Connections. Galvanized Steel Carriage Bolt, Nut and Lockwasher included. Dual-Rated for use on Aluminum, ACSR and Copper Conductors. |
| Application | Securing Conductors |
| Size | Bolt Head 3/4 inch, Bolt Size 1/2 inch, Height 3-1/4 X Length 3-3/4 X Width 2-1/2 inch |
| Connection | Bolted |
| Conductor Range | Main: 336.4 to 1/0 ACSR ; 1/0 to #6 Armored Rod ACSR ; 400 kcmil to 1/0 STR ; 1/0 to #6 Armored Rod AL/CU. Tap: 336.4 kcmil to 1/0 ACSR ; 400 kcmil to 1/0 STR ALCU |
| Number Of Conductors | 2 |
| Material | Aluminum |
| Insulation | None |
| Mounting | None |
| Environmental Conditions | All Seasons / Conditions |

Packaging

| | |
|---------------------------|---------------|
| Outer Quantity | 20 |
| Outer Dimensions (inches) | 14x6.2x7 |
| Weight Uom | 1.1 lbs. Each |

Documents / Support Tools

| | |
|--------------------------------|----------------------|
| Technical Drawing / Data Sheet | Available on Website |
| Catalog | Available on Website |

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com