

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft., Black

MODEL NUMBER: P004-004



Black computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 4 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to four feet. The four-foot length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- 4 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, servers and monitors to a PDU up to 4 ft. away in your data center
- Extend an existing power connection up to 4 ft. to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-004 C14 Male to C13 Female Power Cable, 4 ft., Black

Specifications

OVERVIEW	
UPC Code	037332156402
Country/Region	North America
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Maximum Input Amps	10
Cable Length (ft.)	4
Cable Length (m)	1.2
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Weight (kg)	0.19
Shipping Weight (lbs.)	0.42
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>