

## European Computer Power Cord, C5 to Schuko, 2.5A, 250V, 17 AWG, 6 ft. (1.8 m), Black

MODEL NUMBER: P058-006



C5 to Schuko EU power cord connects your notebook computer or laptop with a 3-slot C6 power inlet to a Schuko outlet.

### Features

**European Computer Power Cord Connects Notebook Computers to a Schuko AC Outlet** This C5 to Schuko power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other Schuko outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The six-foot (1.8-meter) length allows you flexibility in placing equipment with respect to the power outlet.

### Highlights

- EU power cable recommended for powering notebooks and laptops with C6 inlets
- 6 ft. (1.8 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

### Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

### Package Includes

- P058-006 C5 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black

## Specifications

OVERVIEW	
UPC Code	037332153647
Country/Region	Europe
INPUT	
Maximum Input Amps	2.5
Cable Length (ft.)	6
Cable Length (m)	1.8



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Voltage Compatibility (VAC)	250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	24.13 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	9.50 x 7.10 x 0.50
Shipping Weight (kg)	0.21
Shipping Weight (lbs.)	0.46
Wire Gauge (AWG)	17
Wire Gauge (OD - mm <sup>2</sup> )	1.15
<b>CONNECTIONS</b>	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	IEC-320-C5
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>