

Envi-Ro-Tech[™] 1678

Light Duty Cleaner 1678

Introduction

Light duty defluxer for type R and water-soluble fluxes. Can be used as cleaner to remove light oils, polar soils and white residue. Drying agent for water, and removes water stains and mineral traces. Does not contain CFCs or 1,1,1-Trichloroethane.

Features / Benefits

Non-Flammable Rapidly Evaporating Zero Residue Non-Corrosive

Physical Properties	
Boiling Point	35°C / 90°F
Flash Point (TCC)	None
Evaporation Rate	>1
Surface Tension	
Kauri-Butanol (KB Value)	

70-75%-Aerosol 75%-Bulk <25%-Aerosol 25%-Bulk 4.1%-Aerosol 4.25%-Bulk <5%

Chemical Components

Dichlorofluoroethane(1717-00-6)	
Ethyl Alcohol	
Methanol(67-56-1)	
Carbon Dioxide (Aerosol Propellant) (124-38-9)	

Plastic Compatibility

Material	Compatibility	Material	Compatibility
ABS	Not Compatible	РММА	Not Compatible
Nylon	Excellent	РОМ	Excellent
Lexan	Not Compatible	PP	Excellent
HDPE	Excellent	PS	Not Compatible
CDPE	Excellent	PTFE	Excellent
C. E. Phenolic	Excellent	PVC	Excellent

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

Envi-Ro-Tech[™] 1678 is available in the following sizes:

1678-12S	12 Ounce Aerosol
1678-22S	22 Ounce Aerosol
1678-G	1 Gallon in Glass
1678-5G	45 Pounds in Metal

Resources

Techspray $\ensuremath{\mathbb{R}}$ products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: <u>www.techspray.com</u>.

North America Tech Spray L.P. P.O. Box 949 Amarillo, TX 79105 800-858-4043 email: tsales@techspray.com

Europe

Techspray International UNIT 4, 44/46 Bunyan Road, Kempston Bedford MK42 8HL United Kingdom +44 (0) 1234 855443 email: tseurope@techspray.com

Countries Outside US Call to locate a distributor

in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P. P.O. Box 949 Amarillo, TX 79105 www.techspray.com Aerosol MSDS English French German Italian Spanish

Bulk MSDS English French German Italian Spanish





Copyright 2003 Tech Spray, L. P. For Commercial Use Only