

## USB 2.0 Panel Mount Extension Cable (B to Panel Mount B M/F), 1 ft.

MODEL NUMBER: U025-001-PM



### Description

This 1-ft Panel Mount USB extension cable is manufactured using USB2.0 cable. It features a panel mount connector that allows you to secure a USB B female port in a fixed location, for custom solutions such as an internally mounted drive. It is designed for use with USB 2.0 devices, but is backwards compatible and can also be used with USB 1.1. Made with superior foil shielding for reliable error-free data communications. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

### Features

- Add a fixed USB B female port to a custom solution, such as an internally mounted drive
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/20 AWG data lines

## Specifications

OVERVIEW	
UPC Code	037332178473
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	

### Highlights

- Add a fixed USB B female port to a custom solution, such as an internally mounted drive
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines

### System Requirements

- Any device requiring a longer USB cable

### Package Includes

- U025-001-PM 1-ft. Panel Mount USB 2.0 Extension Cable (USB B M/F)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
Shipping Dimensions (hwd / cm)	0.64 x 2.54 x 15.24
Shipping Dimensions (hwd / in.)	0.25 x 1.00 x 6.00
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.05
<b>CONNECTIONS</b>	
Side A - Connector 1	USB B (MALE)
Side B - Connector 1	USB B (FEMALE) - PANEL MOUNT
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	USB 2.0 (High Speed); USB
<b>CERTIFICATIONS</b>	
Certifications	RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>