




Duster

1671

Techspray air dusters blow away dust, microscopic contaminants, lint, metallic oxide deposits and other soils that can damage sensitive electronics. When these contaminants get in the way of vents or fans within the device, they create a build up which leads to overheating and/or shortages.

Properly cleaning your electronics on a regular basis keeps your systems cool and working optimally, extending the life of the product. If you begin to notice your fans are becoming increasingly loud, or your systems are not running as efficiently, it may be time to treat them.

Choose the gas duster best suited for your application.



Non-flammable & 100% HFC-134a duster
Canned Tetrafluoroethane is the perfect solution to safely maintain the life of your most sensitive electronics and devices. Effectively get rid of harmful dust and debris and keep your devices and systems running smoothly. This product leaves zero residue, is safe to use on plastics and moisture free.

All of our gas dusters and other products meet federal, state and local government regulations and are created with the goal of a clean and safe environment.

100% nonflammable HFC-134a based duster.

- 100% pure HFC-134a
- Non-flammable
- Non-ozone depleting
- Moisture free
- Zero residue
- Safe on plastics
- VOC exempt
- Velocity 11.3 m/s
- Safest choice for energized equipment

Specifications:

- GM HMA 12993-F
- Delco C00012555



Product Packaging

1671-10S
Duster
10 oz
12 units/case



1671-15S
Duster
15 oz
12 units/case



Technical Information

Chemical Composition

CHEMICAL NAME	CAS #
1,1,1,2-Tetrafluoroethane (aerosol)	811-97-2

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2016 Techspray, A Division of ITW



Techspray
8125 Cobb Center Drive,
Kennesaw, GA 30152
800-858-4043 • www.techspray.com

