

USB to RJ45 Cisco Serial Rollover Cable, USB Type-A to RJ45 M/M, 6 ft.

MODEL NUMBER: U209-006-RJ45-X



Connects your computer or laptop's USB port to your Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port.

Description

The U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable is designed for consumers and IT professionals who want to connect their computer or laptop's USB port to their Cisco® modem, router, firewall, switch or other serial-based Cisco device with a console port. Convenient six-foot cable eliminates the need for additional cables or adapters. Install the drivers using the included CD, then attach the RJ45 plug to your Cisco device and the USB plug to your computer for a direct connection (Note: If your computer has no CD drive, the drivers are available online for you to download). No external power is required. Works with older and new Cisco models. Supports data transfer rates up to 250 Kbps, as well as remote wake-up and power management. Premium double shielding eliminates crosstalk and reduces EMI/RFI line noise that could negatively affect your transfer speeds and data. Compatible with Windows®, Mac® and Linux.

Features

Connects Computer's USB Port to Cisco Device Connect computer or laptop to Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port
Works with older and new Cisco models
6 ft. long

Top-of-the-Line Performance Supports data transfer rates up to 250 Kbps
Supports remote wake-up and power management
Utilizes FTDI chipset.

Premium Double Shielding Eliminates crosstalk and reduces EMI/RFI line noise that could negatively affect transfer speeds and data

Easy to Use No other cables or adapters needed
No external power required
Driver CD included (drivers also available online for download if your computer has no CD drive)

Highlights

- Supports data transfer rates up to 250 Kbps
- Supports remote wake-up and power management
- Double shielding reduces crosstalk and EMI/RFI line noise
- Compatible with Windows, Mac and Linux
- No cables, adapters or external power required

System Requirements

- Computer with available USB port
- Cisco device with available RJ45 console port
- Windows, Mac or Linux operating system

Package Includes

- U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable
- Driver CD
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332190017
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Gray
Shipping Dimensions (hwd / cm)	3.05 x 11.94 x 10.41
Shipping Dimensions (hwd / in.)	1.20 x 4.70 x 4.10
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Technology	USB
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>