



E-Line Blue Shower Maintenance Cleaner Product# 1620-10S

Product Description

E-Line is a hydrocarbon-based cleaner formulated to be powerful, yet very economical. Eliminate brushing and scrubbing, saving time and materials. Clean oil and contaminants off of metal parts, printed circuit boards, barcode instruments, switch boxes, gearboxes, and engines.

Maintenance cleaners clean oil and contaminants off of metal parts, printed circuit boards, barcode instruments, switch boxes, gearboxes, and engines. Techspray® has produced Blue Shower® maintenance cleaners for over 30 years, making Blue Shower a staple in maintenance departments all over the world!

Features / Benefits

- Powerful cleaner
- Ideal for sensitive plastics
- Low toxicity
- Zero residue
- Non-ozone depleting
- NSF registered K1 and K2

Usage Instructions

Disconnect equipment from power source. Hold can 6-8 inches away. When used as a general cleaner, start at top of area to be cleaned using a sweeping motion and spray the area, slowly working toward the bottom. To clean in hard to reach areas, insert extension tube in sprayhead. Allow components to dry completely before applying current.

Approvals

FORD TOX #142430, NSF registered K1 and K2

Plastics & Rubber Compatibility

MATERIAL NAME	RATING
ABS:	Excellent
Nylon:	Excellent
Lexan:	Excellent
HDPE:	Excellent
LDPE:	Excellent
C.E. Phenolic:	Excellent
PMMA:	Excellent
POM:	Excellent
PP:	Excellent
PS:	Excellent
PTFE:	Excellent
PVC:	Excellent



Typical Product Data and Physical Properties

Odor:	Characteristic
Appearance:	Clear, colorless liquid
Percent Volatile:	100 at 20°C (68°F)
Vapor pressure:	55.49 mmHg @20C (VOC Composite Vapor Pressure)
Flashpoint and method:	(22°F) TAG CC
Solubility in water:	to 32 at 20°C (68°F)
Evaporation rate:	>1 (TCE=1)
Density:	0.713g/mL at 25°C
VOC:	Aerosol 75%
Shelf life:	5 years

E-Line Blue Shower Maintenance Cleaner Product# 1620-10S

Packaging and Availability

1620-10S 10 oz. Aerosol

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.