

Universal Reversible USB 2.0 Cable (Reversible A to B M/M), 3 ft.

MODEL NUMBER: UR022-003



Reversible USB "A" connector plugs in any direction

Description

Tripp Lite's UR022-003, 3-ft. USB2.0 A/B device cable, with Universal / Reversible "A" connector, meets or exceeds USB 2.0 specifications. No guessing on how to plug into the Computer or Hub port... Connects in either direction. Backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- 3ft, USB 2.0 A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332179432
INPUT	

Highlights

- 3ft, USB 2.0, A/B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 A-Male to B-Male Device Cable - 3ft



Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	0.64 x 12.19 x 17.78
Shipping Dimensions (hwd / in.)	0.25 x 4.80 x 7.00
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Wire Gauge (AWG)	28/24
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
FEATURES & SPECIFICATIONS	
Technology	USB 2.0 (High Speed); USB
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>