

Up-Angle Cat6 Gigabit Molded UTP Ethernet Cable (RJ45 Right Angle Up M to RJ45 M), Blue, 10ft.

MODEL NUMBER: N204-010-BL-UP



Highlights

- Space saving design
- Up Angle connector to Straight
- Cat6 Gigabit rated

System Requirements

- Use with Cat6, Cat5e, Cat5, or VoIP networks

Package Includes

10ft Blue Cat6 Up Angle to Straight RJ45 - RJ45 Patch cable

Description

Tripp Lite's Angled Cat6 Patch Cables are ideal for where connections are in tight quarters. Choose from Up, Down, Left, and Right angled cables, depending on your situation. Reduces stress on the cable, and excessive bending. Great for switches and patch panels in networking racks, or behind desks and wall connections. Meets or exceeds Cat6 specifications. Fully molded ends for a lifetime of use.

Features

- 10ft Blue Cat6, Up Angle to Straight RJ45 - RJ45 Patch cable
- PVC 4 Pair Stranded Conductors, 24AWG
- Fully Molded Ends
- ETL Verified to TIA/EIA -568-B
- 550Mhz Gigabit Speed Rated

Specifications

OVERVIEW	
UPC Code	037332167613
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120



Cable Length (cm)	304.8
PHYSICAL	
Cable Shielding	UTP
Color	Blue
Shipping Dimensions (hwd / cm)	1.27 x 16.51 x 17.02
Shipping Dimensions (hwd / in.)	0.50 x 6.50 x 6.70
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Snagless Connector	No
Wire Gauge (AWG)	24
Wire Type	Stranded
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE) - UP ANGLE
FEATURES & SPECIFICATIONS	
Technology	Cat5/5e; Cat6
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>