



Log on

[Log on as distributor](#)

Search product

Navigation

- ▶ Main page
- ▶ Products
- ▶ Find a dealer
- ▶ Support
- ▶ Publications
- ▶ Jobs
- ▶ About us

News

**K8055, K8055N, VM110, VM110N iPhone Application**

iPhone application for K8055, K8055N (kit) or VM110,...

Posted on 02-11-13

[Read more...](#)

**K8055, K8055N, VM110, VM110N Android Application**


Android application for K8055, K8055N, VM110 & VM110NUSB...

Posted on 09-20-11

[Read more...](#)

[PRODUCT OVERVIEW](#) ▶ [VELLEMAN KITS & OSCILLOSCOPES](#) ▶ [MINIKITS](#)

## VOICE RECORDING/PLAYBACK MODULE




**MK195**

Popular item

Support

[Downloads \(3\)](#)

[Support](#)



### Features

- recording time between 30 and 90 s (adjust the sample rate)
- on-board microphone
- speaker Ø 57 mm included
- using the speed adjustment, a "funny voice" can be created
- external open-collector trigger inputs for recording, playback, delete, next, and volume

### Specifications

- power supply : 9 ... 12 VDC or with a 9 V battery (ex. 6LI61)
- power consumption:
  - max. 150mA during playback
  - max. 6mA during standby!
- adjustable sampling rate: 5...12 kHz
- speaker output: 500 mW max., 8 ohm
- nominal recording time: 60 seconds
- PCB dimensions: 2.6 x 2 x 0.8"

*All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.*

[REACH communicating information according to article 33 WEEE](#)



Find us on **facebook**<sup>®</sup>

Follow us on **twitter**

[forum.velleman.eu](http://forum.velleman.eu)

Advertisements

**ACCREDITED BUSINESS**

BBB

CLICK HERE FOR BBB BUSINESS REVIEW

3 4 7 8

Set All Digital Clear All Digital

A1

**K8055(N) / VM110(N)**

iPhone APP

**VM201**

Download appl

8055 Series

Card Address

SA12 SA13

Connect

A1 A2

Inputs

**K8055(N) / VM110(N)**

ANDROID APPLICATION

velleman<sup>®</sup> Inc.

SUBSCRIBE TO OUR NEWSLETTER

**K8090**

8-CHANNEL USB RELAY CARD