



Log on

[Log on as distributor](#)

Search product

Search Product

Navigation

- ▶ Main page
- ▶ Products
- ▶ Find a dealer
- ▶ Support
- ▶ Publications
- ▶ Jobs
- ▶ About us

News

K8055, K8055N, VM110, VM110N iPhone Application

iPhone application for K8055, K8055N (kit) or VM110,...

Posted on 02-11-13

[Read more...](#)

K8055, K8055N, VM110, VM110N Android Application

Android application for K8055, K8055N, VM110 & VM110NUSB...

Posted on 09-20-11


[Read more...](#)

[PRODUCT OVERVIEW](#) ▶ [ELECTRONIC COMPONENTS](#) ▶ [ENCLOSURES](#) ▶ [ENCLOSURES - G-SERIES](#) ▶ [GBS SERIES \(SEALED DIE-CAST ALUMINUM ENCLOSURES WITH FLANGE\)](#)

SEALED DIE-CAST ALUMINUM CASE WITH FLANGE



GBS11MF
Support
[Support](#)



Enclosures for sensitive electronic assemblies and for pneumatic, hydraulic and electrical devices in commercial and industrial environments. These enclosures provide effective EMI and RFI shielding. Designed according to IP65 of IEC529 and NEMA4 (dust- and hoseproof).
The mounting holes and the fixing screws for the lid are located outside the sealed area, which prevents moisture and dust from entering the enclosure.
The lid incorporates a recessed neoprene gasket.
Bosses on the internal base allow the fixing of PCB's and are suited for an earthing connection, etc...
Internal guide slots allow vertical PCB mounting.
The lid-mounting screw holes are threaded and the screws themselves are captive and recessed.
Two or four holes make horizontal PCB mounting possible.

Features

- material: aluminum alloy

Specifications

- dimensions: 8 47/64" x 5 3/4" x 2 11/64"
- drawing:
 - o L: 252mm
 - o L1: 222,3mm
 - o W: 146,1mm
 - o W1: 117,7mm
 - o H: 55,5mm
 - o C1: 211,7mm
 - o C2: 135,6mm
 - o C3: 238mm
 - o C4: 98mm
 - o S1: 100,1mm
 - o L2: 205,9mm
 - o L3: 213,7mm
 - o L4: 218,6mm
 - o W2: 129,2mm
 - o W3: 137,8mm
 - o W4: 142mm
 - o H1: 48,9mm

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

[REACH communicating information according to article 33 WEEE](#)



forum.velleman.eu

Advertisements

3 7
4 8
Set All Digital Clear All Digital
A1
K8055(N) / VM110(N)
iPhone APP

K8090
8-CHANNEL USB RELAY CARD

ACCREDITED BUSINESS
BBB.

CLICK HERE FOR
BBB BUSINESS REVIEW

VM201
Download appl

velleman® Inc.
SUBSCRIBE TO OUR
NEWSLETTER

K8055(N) / VM110(N)
ANDROID APPLICATION