

**Clamping yoke
KLBUE 4-13.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE 4-13.5
Order No.	1592810000
Version	Clamping yoke, Clamping yoke, Steel
GTIN (EAN)	4008190182250
Qty.	10 pc(s).

**Clamping yoke
KLBUE 4-13.5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	20.5 mm	Width (inches)	0.807 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	31.5 mm	Depth (inches)	1.24 inch
Net weight	15.5 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C		

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting, Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------


Dimensions

Pitch in mm (P)	20 mm
-----------------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
eClass 9.0	27-14-11-50	eClass 9.1	27-14-11-50
eClass 10.0	27-14-11-50	UNSPSC	30-21-18-01

Approvals

Approvals	
-----------	---

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Attestation of Conformity EAC certificate
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN_WSCAD
Engineering Data	STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks