


Data sheet | Item number: 281-512/281-501

Fuse plug; with pull-tab; for miniature metric fuses 5 x 20 mm and 5 x 25 mm;
with LED indicator; 24 V AC/DC; 6 mm wide; gray



www.wago.com/281-512_281-501



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Subject to changes.

RoHS 
Compliant

BOMcheck.net

Color: 

Item description

Safety information 1:

Electrical ratings are given by the fuse and blown fuse indication.

Safety information 2:

Leakage current in case of a blown fuse: LED 5 ... 20 mA

Data

Electrical data

Voltage type (1)	AC/DC
------------------	-------

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	250 V
-------------------------	-------

Rated current	6.3 A
---------------	-------

Geometrical Data

Width	6 mm / 0.236 inch
-------	-------------------

Mechanical data

Marking level	Center marking
---------------	----------------

Material Data

Color	gray
-------	------

Insulating material	Polyamide 66 (PA 66)
---------------------	----------------------

Fire load	0.081 MJ
-----------	----------

Weight	6.7 g
--------	-------

Commercial data

Product Group	1 (Rail Mounted Terminal Blocks)
---------------	----------------------------------

Packaging type	BOX
----------------	-----

Country of origin	CN
-------------------	----

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com





Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

GTIN	4050821276265
Customs Tariff No.	85366990990

Compatible products

General accessories

	Item no.: 281-503 Shorting link; 5 x 20 mm; if the fuse plug is used as disconnect plug	www.wago.com/281-503
	Item no.: 281-610 3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®; 4,00 mm ² ; gray	www.wago.com/281-610
	Item no.: 281-656 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®; 4,00 mm ² ; gray	www.wago.com/281-656
	Item no.: 281-916 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®; 4,00 mm ² ; gray	www.wago.com/281-916















Marking accessories

	Item no.: 2009-114 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; white	www.wago.com/2009-114
	Item no.: 2009-114/000-002 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; yellow	www.wago.com/2009-114/000-002
	Item no.: 2009-114/000-005 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; red	www.wago.com/2009-114/000-005
	Item no.: 2009-114/000-006 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; blue	www.wago.com/2009-114/000-006
	Item no.: 2009-114/000-007 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; gray	www.wago.com/2009-114/000-007
	Item no.: 2009-114/000-012 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; orange	www.wago.com/2009-114/000-012
	Item no.: 2009-114/000-023 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; green	www.wago.com/2009-114/000-023

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

	Item no.: 2009-114/000-024 WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; violet	www.wago.com/2009-114/000-024
	Item no.: 209-701 WSB marking card; as card; not stretchable; plain; snap-on type; white	www.wago.com/209-701
	Item no.: 209-701/000-002 WSB marking card; as card; not stretchable; plain; snap-on type; yellow	www.wago.com/209-701/000-002
	Item no.: 209-701/000-005 WSB marking card; as card; not stretchable; plain; snap-on type; red	www.wago.com/209-701/000-005
	Item no.: 209-701/000-006 WSB marking card; as card; not stretchable; plain; snap-on type; blue	www.wago.com/209-701/000-006
	Item no.: 209-701/000-007 WSB marking card; as card; not stretchable; plain; snap-on type; gray	www.wago.com/209-701/000-007
	Item no.: 209-701/000-012 WSB marking card; as card; not stretchable; plain; snap-on type; orange	www.wago.com/209-701/000-012
	Item no.: 209-701/000-017 WSB marking card; as card; not stretchable; plain; snap-on type; light green	www.wago.com/209-701/000-017
	Item no.: 209-701/000-023 WSB marking card; as card; not stretchable; plain; snap-on type; green	www.wago.com/209-701/000-023
	Item no.: 209-701/000-024 WSB marking card; as card; not stretchable; plain; snap-on type; violet	www.wago.com/209-701/000-024
	Item no.: 793-4501 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; white	www.wago.com/793-4501
	Item no.: 793-4501/000-002 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; yellow	www.wago.com/793-4501/000-002
	Item no.: 793-4501/000-005 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; red	www.wago.com/793-4501/000-005
	Item no.: 793-4501/000-006 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; blue	www.wago.com/793-4501/000-006

Subject to changes.



Item no.: 793-4501/000-007
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; gray

www.wago.com/793-4501/000-007



Item no.: 793-4501/000-012
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; orange

www.wago.com/793-4501/000-012



Item no.: 793-4501/000-014
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; brown

www.wago.com/793-4501/000-014



Item no.: 793-4501/000-023
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; green

www.wago.com/793-4501/000-023



Item no.: 793-4501/000-024
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; violet

www.wago.com/793-4501/000-024

clamps



Item no.: 280-510
Triple-deck terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; green-yellow/blue/gray www.wago.com/280-510



Item no.: 280-514
Double-deck terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray /gray www.wago.com/280-514



Item no.: 280-528
Double-deck terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray /gray www.wago.com/280-528



Item no.: 280-531
Double-deck terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; blue /gray www.wago.com/280-531



Item no.: 280-532
Double-deck terminal block; with additional jumper position on lower level; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; blue/gray www.wago.com/280-532



Item no.: 280-889
Triple-deck terminal block; with additional jumper position on lower level; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray/gray/gray www.wago.com/280-889



Item no.: 280-891
Double-deck terminal block; with additional jumper position on lower level; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray/gray www.wago.com/280-891

Downloads

Documentation

Bid Text

281-512/281-501

Mar 14, 2017

doc

Download

Subject to changes.



doc - Datei			24.6 kB	
281-512/281-501	Feb 19, 2019	xml	3.1 kB	Download
X81 - Datei				
Additional Information				
Technical explanations	Apr 3, 2019	pdf	2.1 MB	Download

CAD/CAE-Data

CAD data


2D/3D Models 281-512/281-501		URL		Download
------------------------------	--	-----	--	----------

CAE data

WSCAD Universe 281-512/281-501				Download
--------------------------------	--	--	--	----------

Installation Notes

Subject to changes.




Length of carrier terminal blocks with a fuse plug:

59 mm / 2.32 inch for 281-916

73.5 mm / 2.89 inch for 281-610

86 mm / 3.39 inch for 281-656

Testing



Using fuse plugs with rail-mount terminal blocks for control circuit protection is highly advantageous because the function and wiring levels are separated:

- No additional cost for assembly and wiring
-

Subject to changes.




- No risk of accidental contact with live parts when disconnecting the fuse plug
-
- The fuse plug is completely separated from the carrier terminal block when replacing a fuse – away from current carrying parts
-
- The fuse plug can be removed by service personnel
-
- No unintentional reclosing of the circuit by another person
-
- Quickly exchange a fuse by using a prepared “stand-by plug”
-

Fuse plug features for quick and safe applications:

- Optional LED indicates blown fuse
-
- Top-of-unit marking slot provides clear carrier terminal block identification
-
- Two test slots with touch contacts
-
- Terminal blocks/plugs provide high-density wiring in a width of just 6 mm
-
- May be used as a disconnect plug in combination with a shorting link
-

Subject to changes.



When a corresponding neutral circuit is adjacent to the fuse plug, a 5 mm wide space-saving terminal block may be used, as a 6 mm fuse plug may overlap the terminal block (see diagram).

For 5 mm wide carrier terminal blocks can be used with end plates, for example.

Subject to changes.