

**Cutting, stripping and crimping tool
STRIPAX PLUS 2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Cutting, stripping and crimping tools for
connected wire-end ferrules strips**

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved

General ordering data

Type	STRIPAX PLUS 2.5 ZERT
Order No.	9011980000
Version	Cutting, stripping and crimping tool, Crimping tool for wire-end ferrules, 0.5mm ² , 2.5mm ² , Trapezoidal crimp
GTIN (EAN)	4008190004613
Qty.	1 pc(s).

Creation date April 21, 2020 12:57:16 PM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.

**Cutting, stripping and crimping tool
STRIPAX PLUS 2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	210 mm	Width (inches)	8.268 inch
Weight	260 g	Net weight	307 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Description of contact

Type of contact	Strips of linked wire-end ferrules	Crimping range, min.	0.5 mm ²
Crimping range, max.	2.5 mm ²	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 20		

tool data crimping

Crimping profile 1, min.	0.5 mm ²	Crimping type/profile	Trapezoidal crimp
Crimping profile 1, max.	0.75 mm ²	Crimping profile 2, min.	1 mm ²
Crimping profile 2, max.	1.5 mm ²	Crimping profile 3, min.	2.5 mm ²

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
eClass 9.0	21-04-37-06	eClass 9.1	21-04-37-06
eClass 10.0	21-04-37-06	UNSPSC	31-16-31-02

Approvals

Approvals


Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
User Documentation	Manual

Data sheet

**Cutting, stripping and crimping tool
STRIPAX PLUS 2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use



Example of use



Example of use

