


**Accessories**  
**TS 35X15/LL 1M/ST/ZN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**General ordering data**

Type	TS 35X15/LL 1M/ST/ZN
Order No.	<a href="#">0236510000</a>
Version	Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated
GTIN (EAN)	4008 190017699
Qty.	1 m

Creation date August 17, 2020 9:32:41 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

## Accessories TS 35X15/LL 1M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	35 mm	Width (inches)	1.378 inch
Height	35 mm	Height (inches)	1.378 inch
Depth	15 mm	Depth (inches)	0.591 inch
Net weight	630 g		

### Mounting rail

Drill-hole diameter	5.2 mm	Short circuit strength corresponds to E-Cu wire	50 mm <sup>2</sup>
Short-time withstand current according to IEC 60947-7-2	6 kA/1s	Slit gap	11 mm
Slit length	25 mm	Slit width	5.2 mm
Slotted drill holes	Yes	Solder eyelet hole diameter (D)	5.2 mm
Spacing of holes, centre-to-centre	36 mm	Thickness	1.5 mm

### Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
eClass 9.0	27-40-06-02	eClass 9.1	27-40-06-02
eClass 10.0	27-40-06-02	UNSPSC	30-21-18-01

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 4.1 ELECTR 16/17 EN</a> <a href="#">CAT 1 TERM 16/17 EN</a> <a href="#">CAT 2 PORTFOLIOGUIDE EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>