

ESG ESG 6/17 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	ESG 6/17 K MC NE WS
Order No.	1880120000
Version	ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4032248478804
Qty.	200 pc(s).
compatible printer	1324380000 2438520000 2438510000

ESG
ESG 6/17 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	17 mm	Width (inches)	0.669 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.34 g		

General data

Adhesive	Double-sided adhesive tape	Application/manufacturer	Self-adhesive
Colour	white	Halogen	No
Material	PA 66	Material colour according to resistance code	9
Operating temperature range	-40... 100 °C	UL 94 flammability rating	V-2
Version	Self-adhesive	Width	17 mm

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29
eClass 10.0	27-40-06-29	UNSPSC	30-21-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Product Change Notification	Technical change to MultiCard material - DE Technical change to MultiCard material - EN
Software	M-Print PRO configuration file

Data sheet

ESG
ESG 6/17 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

