

**Pressing tool  
PZ 6/5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Type	PZ 6/5
Order No.	<a href="#">9011460000</a>
Version	Pressing tool, Crimping tool for wire-end ferrules, 0.25mm <sup>2</sup> , 6mm <sup>2</sup> , Trapezoidal indentation crimp
GTIN (EAN)	4008190165352
Qty.	1 pc(s).

**Data sheet**

**Pressing tool  
PZ 6/5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	423 g	Net weight	459 g

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Technical data**

Version	Mechanical, without interchangeable inserts
---------	---

**Description of contact**

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.25 mm <sup>2</sup>
Crimping range, max.	6 mm <sup>2</sup>	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 24		

**tool data crimping**

Crimping profile 1, min.	0.25 mm <sup>2</sup>	Crimping type/profile	Trapezoidal indentation crimp
Wire end ferrules cross-section, min.	0.25 mm <sup>2</sup>	Crimping profile 1, max.	0.5 mm <sup>2</sup>
Wire end ferrules cross-section, max.	6 mm <sup>2</sup>	Crimping profile 2, min.	0.75 mm <sup>2</sup>
Crimping profile 2, max.	1.5 mm <sup>2</sup>	Crimping profile 3, min.	2.5 mm <sup>2</sup>
Crimping profile 4, min.	4 mm <sup>2</sup>	Crimping profile 5	6 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
eClass 9.0	21-04-38-11	eClass 9.1	21-04-38-11
eClass 10.0	21-04-38-11	UNSPSC	31-16-31-02

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a> <a href="#">CAT 2 PORTFOLIOWGUIDE EN</a>
Engineering Data	<a href="#">WSCAD</a>

**Data sheet**

**Pressing tool  
PZ 6/5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

