

**Pressing tool
PZ 4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 4
Order No.	9012500000
Version	Pressing tool, Crimping tool for wire-end ferrules, 0.5mm ² , 4mm ² , Trapezoidal crimp
GTIN (EAN)	4008 190090920
Qty.	1 pc(s).

Creation date August 16, 2020 2:04:04 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Data sheet

**Pressing tool
PZ 4**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	448 g	Net weight	425.6 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---------------------------------------------

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.5 mm ²
Crimping range, max.	4 mm ²	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 21		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, min.	0.5 mm ²
Wire end ferrules cross-section, max.	4 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
eClass 9.0	21-04-38-11	eClass 9.1	21-04-38-11
eClass 10.0	21-04-38-11	UNSPSC	31-16-31-02

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD
User Documentation	Manual

Data sheet

**Pressing tool
PZ 4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

