



JavaScript seems to be disabled in your browser.

You must have JavaScript enabled in your browser to utilize the functionality of this website.

Wiha Tools USA - selling **Wiha** made hand tools in the United States since 1985



+ SHIPS FREE
UPS FLAT RATE

**MILITARY
DISCOUNT
IBEW-NECA
DISCOUNT**

800-494-6104 Cart ▾

[Account](#) | [Quick Order](#) | [Log In](#) | [Contact Us](#) | [Checkout](#)

[Wiha Tools No Hassle Guarantee](#)

Menu

- [Torx](#) +
- [Torque Tools](#) +
- [Tech Tools](#) +
- [Shop Tools](#) +
- [Screwdrivers](#) +
- [Pliers](#) +
- [Insulated Tools](#) +
- [Hex](#) +
- [ESD Safe](#) +
- [Bits & Sets](#) +
- [Best Sellers](#)

[Home](#) → [Tool Types](#) → [Pliers and Cutters](#) → [Insulated Diagonal Cutters 5.5"](#)

Insulated Diagonal Cutters 5.5"





Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Insulated Diagonal Cutters 5.5" (AWG #6)

SKU: 32830

Add to Cart

Qty:

1

[See additional sizes available](#) [Share on Facebook](#) [Tweet This](#) [Pin it](#)

Frequently bought together



Add selected to cart

This item: [Insulated Diagonal Cutters 5.5"](#)

[General Purpose Zipper Bag](#)

Details


Insulated 1000 Volt Rated, 10,000 Volt Tested
Made By Wiha from High Quality Forged CV Tool Steels
Individually Tested & Meet VDE, EN/IEC ASTM, NFPA, CSA, ISO
Induction Hardened Cutting Edges and Jaws
Heavy Duty Steel Riveted Joints
Multi-Layered Hard Chrome Finish, Best Anti-Corrosion Surface
All Tools Individually Tested for insulation Integrity
Ergo Molded Insulated Cushioned Grips.
Guaranteed Wiha Made Quality, 100% Tested Insulated Tools

Additional Info

Packaging	Vinyl Pouch
SKU	32830
Weight (lbs)	0.4600
California Residents	Click for Proposition 65 warning
Grip Type	Insulated
AWG	#6
Pliers Type	Diagonal

Overall Length	5.5"
Jaw Opening	.83"
Jaw Length	.77"
Jaw Thickness	.39"
Jaw Width	.75"
UPC	084705328300
UNSPSC	27112135

You may also be interested in the following product(s)



Insulated Stripping Pliers

Insulated Stripping Pliers 10-20 AWG

Insulated Round Nose Pliers 6.3"

Insulated Ratcheting Cable Cutter 750 MCM 11"

Customer Reviews



Ask a Question

Write a Review

Reviews **0** Questions **0**



Be the first to review this item

Wiha Professional Quality Hand Tools



Wiha Tools are covered by a No Hassle Guarantee

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)
[Press](#)
[Authorized Distributor Login](#)
[Privacy Policy](#)

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday office hours 8AM - 5PM
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591

[Download Catalogs](#)
[Discounts and promotions](#)
[Military Discount](#)
[IBEW-NECA Discount](#)
[Wiha Manufacturing and Compliance](#)
[Wiha Tools USA Blog](#)
[Filter and sort all Wiha hand tools](#)
[Complete list of tools](#)

[Terms and Conditions](#)
[Check the status of your order](#)
[Having technical issues with the website?](#)



4.8 ★★★★★
Google
Customer Reviews

Fax: 763-295-6598

[Shipping](#)
[Returns](#)
[Warranty Info](#)
[Frequently Asked Questions](#)
[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)
**Over 5000 Professional Quality Wiha Tools
In Stock**

