

Home → Tool Types → Torque Screwdrivers → TorqueFix In/lbs Pre-Set Handles

Quickly see and find recommended torque blades for this handle

# TorqueFix In/lbs Pre-Set Handles



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Nm	Price	Qty
28503	TorqueFix Pre-Set Handle 5 In/lbs	0.56		0
28505	TorqueFix Pre-Set Handle 7.5 In/lbs	0.84		0
28507	TorqueFix Pre-Set Handle 10 In/lbs	1.12		0
28509	TorqueFix Pre-Set Handle 12.5 In/lbs	1.41		0
28511	TorqueFix Pre-Set Handle 15 In/lbs	1.69		0
28513	TorqueFix Pre-Set Handle 20 In/lbs	2.25		0
28515	TorqueFix Pre-Set Handle 25 In/lbs	2.82		0

SKU	Product	Nm	Price	Qty
28517	TorqueFix Pre-Set Handle 30 In/lbs	3.39		0
28518	TorqueFix Pre-Set Handle 35 In/lbs	3.95		0
28519	TorqueFix Pre-Set Handle 40 In/Lbs	4.52		0
28521	TorqueFix Pre-Set Handle 50 In/lbs	5.65		0
28523	TorqueFix Pre-Set Handle 60 In/lbs	6.78		0
28525	TorqueFix Pre-Set Handle 70 In/lbs	7.91		0

Add to Cart

- Add to Wishlist
 Share on Facebook
 Tweet This
 Pin it

We accept

## Details

ASME B107.14m, EN ISO 6789, BS EN 26789 Tools Marked with Serial No. & Include Calibration Certificate

An economical solution for accurate dedicated Torque Control Consistent Fastening Ergonomic Multi-Component Handle, particularly light and compact

Audible and perceptible click when the pre-set torque has been attained ±6% Accuracy

Quality & Accuracy Guaranteed to 5000 Cycles or 1 year

Loosening torque approx. +30% greater than tightening torque

Automatically resets for next torque cycle

## Additional Info

Country of Manufacture	Germany
TorqueControl Type	Pre-Set TorqueFix
Handle Grip Types	SoftFinish - cushioned
Torque Display Scale	Inch - lbs

## WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

## Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

## You may also be interested in the following product(s)



## Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

## Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



## Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)  
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm  
CST USA**

1348 Dundas Cir,  
Monticello, MN 55362  
Customer Service Email:  
[cservice@wihatools.com](mailto:cservice@wihatools.com)  
Tel: 763-295-6591  
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools  
In Stock**



**Newsletter** [Subscribe](#)