


+ SHIPS FREE
UPS FLAT RATE
MILITARY DISCOUNT
IBEW-NECA DISCOUNT

100% Lifetime Guarantee

[Best Sellers](#) [On Sale](#)

Home → Tool Types → Pliers and Cutters → MagicTip Straight Internal Safety Ring Pliers

MagicTip Straight Internal Safety Ring Pliers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

[Be the first to review this product](#)

Filter:

SKU	Product	Ring Diameter Range Inch	Ring Diameter Range mm	Tip size inch	Tip size mm	Price	Qty
34610	MT Ring Pliers Internal 3/4- 2-3/8" .070	3/4-2 3/8	19-60mm	.070	1.5mm		0
34611	MT Ring Pliers Internal 1.5 - 4" .090	1 1/2-4	40-100mm	.090	2.3mm		0
34612	MT Ring Pliers Internal 3.5 - 5.5".126	3.5-5.5	85-140mm	.126	3.2mm		0

Add to Cart

[Add to Wishlist](#)
[Share on Facebook](#)
[Tweet This](#)
[Pin it](#)

We accept

Details

High quality C70 forged Tool Steel
Precision and hardened tips manufactured from best Ball-Bearing Steel
Precision notched tips for maximum stability and secure ring holding
Slim Plier Head for optimal Access
Soft Vinyl Grip Handles are Oil and Solvent Resistant
Professional quality made by Wiha

Additional Info

Country of Manufacture	Vietnam
Grip Type	Vinyl
Pliers Type	Retaining Ring
Ring Type	Internal

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure products consistent

with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm CST
USA**

1348 Dundas Cir,
Monticello, MN 55362

Customer Service Email: cservice@wihatools.com

Tel: 763-295-6591

Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

Over 5000 Professional Quality Wiha Tools In Stock



Newsletter

[Subscribe](#)