



## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125295	1.625" Wide x 12" Flatback heatsink 16079 xx2014	1.625	1.312	12	3.2
125296	1.625" Wide x 36" Flatback heatsink 16079 xx2014	1.625	1.312	36	3.2




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125301	2.80" Wide x 12" Flatback Heatsink 11201 XX6998	2.8	1.25	12	2.9
125302	2.80" Wide x 36" Flatback Heatsink 11201 XX6998	2.8	1.25	36	2.9




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125313	2.875" Wide x 12" Flatback heatsink 16078 xx2013	2.875	1.312	12	2.3
125314	2.875" Wide x 36" Flatback heatsink 16078 xx2013	2.875	1.312	36	2.3



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125319	3" Wide x 12" Flatback Heatsink 9099	3	2	12	1.5
125320	3" Wide x 36" Flatback Heatsink 9099	3	2	36	1.5




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125325	3.79" Wide x 12" Flatback heatsink 16304 xx5079	3.79	2	12	1.5
125326	3.79" Wide x 36" Flatback heatsink 16304 xx5079	3.79	2	36	1.5




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125367	4.125" x 12" Flatback Heatsink 2656 xx5138	4.125	1.75	12	1.9
125368	4.125" x 36" Flatback Heatsink 2656 xx5138	4.125	1.75	36	1.9

## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125373	4.375" Wide x 12" Flatback heatsink 16296 xx1527	4.375	1.29	12	1.4
125374	4.375" Wide x 36" Flatback heatsink 16296 xx1527	4.375	1.29	36	1.4




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125397	5.00" Wide x 12" Flatback Heatsink 16338 xx2065	5	1.75	12	1.6
125398	5.00" Wide x 36" Flatback Heatsink 16338 xx2065	5	1.75	36	1.6




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125403	5.375" x 12" Flatback Heatsink 6037 xx5045	5.375	1.312	12	1.8
125404	5.375" x 36" Flatback Heatsink 6037 xx5045	5.375	1.312	36	1.8



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125409	5.50" x 12" Flatback Heatsink 13760 xx2199	5.5	2	12	1.2
125410	5.50" x 36" Flatback Heatsink 13760 xx2199	5.5	2	36	1.2




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125415	6.50" x 12" Flatback Heatsink 6664 xx4509	6.5	1.6	12	1.3
125416	6.50" x 36" Flatback Heatsink 6664 xx4509	6.5	1.6	36	1.3




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125421	6.624" Wide x 12" Flatback heatsink 16524 xx7031	6.624	1.312	12	1.3
125422	6.624" Wide x 36" Flatback heatsink 16524 xx7031	6.624	1.312	36	1.3

## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122255	6.961" Wide x 12" Flatback Heatsink 13694 xx6274	6.961	2.79	12	0.8
125643	6.961" Wide x 36" Flatback Heatsink 13694 xx6274	6.961	2.79	36	0.8




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122256	7.00" Wide x 12" Flatback heatsink 15837	7	2.275	12	0.3
125645	7.00" Wide x 36" Flatback heatsink 15837	7	2.275	36	0.3




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125512	7.20" Wide x 36" Flatback heatsink 16316 xx6438-2	7.2	2.41	36	0.9



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125430	7.343" Wide x 12" Flatback Heatsink 13454 xx4771	7.343	1.312	12	1.1
125431	7.343" Wide x 36" Flatback Heatsink 13454 xx4771	7.343	1.312	36	1.1




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125601	7.574" Wide x 12" Flatback Heatsink 21910	7.574	3.15	12	0.65
125602	7.574" Wide x 36" Flatback Heatsink 21910	7.574	3.15	36	0.65




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125436	8.35" Wide x 12" Flatback Heatsink 13668 xx4937	8.35	2	12	0.9
125437	8.35" Wide x 36" Flatback Heatsink 13668 xx4937	8.35	2	36	0.9

## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122263	8.40" Wide x 12" Flatback heatsink 16681	8.4	1.4	12	0.65
125657	8.40" Wide x 36" Flatback heatsink 16681	8.4	1.4	36	0.65




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122260	9.24" Wide x 12" Flatback Heatsink 19035	9.24	2.535	12	0.62
125651	9.24" Wide x 36" Flatback Heatsink 19035	9.24	2.535	36	0.62




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125520	9.75" Wide x 12" Flatback heatsink 16473 xx5384	9.75	2.28	12	0.75
125521	9.75" Wide x 36" Flatback heatsink 16473 xx5384	9.75	2.28	36	0.75




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125442	9.875" Wide x 12" Flatback heatsink 16329 xx1703	9.875	1.31	12	0.91
125443	9.875" Wide x 36" Flatback heatsink 16329 xx1703	9.875	1.31	36	0.91



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125592	10" Wide x 12" Flatback heatsink 13953 sf1002	10	2.53	12	0.6




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125448	10.25" Wide x 12" Flatback heatsink 14236 xx5772	10.25	2.5	12	0.71
125449	10.25" Wide x 36" Flatback heatsink 14236 xx5772	10.25	2.5	36	0.71




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125454	10.50" Wide x 12" Flatback Heatsink 16990 xx2904	10.5	1.265	12	1.3
125455	10.50" Wide x 36" Flatback Heatsink 16990 xx2904	10.5	1.265	36	1.3

## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125460	10.78" Wide x 12" Flatback Heatsink xx4559	10.78	3.77	12	0.5
125461	10.78" Wide x 36" Flatback Heatsink xx4559	10.78	3.77	36	0.5




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125577	10.827" Wide x 12" Flatback Heatsink 19572	10.827	1.221	12	0.83
125578	10.827" Wide x 36" Flatback Heatsink 19572	10.827	1.221	36	0.83




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122261	11.00" Wide x 12" Flatback Heatsink 19584	11	1.375	12	1.43
125653	11.00" Wide x 36" Flatback Heatsink 19584	11	1.375	36	1.43



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125625	11.811" Wide x 12" Flatback Heatsink 19740	11.811	3.287	12	0.46
125626	11.811" Wide x 36" Flatback Heatsink 19740	11.811	3.287	36	0.46




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125619	11.875" Wide x 12" Flatback Heatsink 17099	11.875	2.594	12	0.4
125620	11.875" Wide x 36" Flatback Heatsink 17099	11.875	2.594	36	0.4




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122262	12.25" Wide x 12" Flatback Heatsink 19152 xx4471	12.25	1	12	1.3
125655	12.25" Wide x 36" Flatback Heatsink 19152 xx4471	12.25	1	36	1.3

## Aluminum Flatback


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125631	12.75" Wide x 12" Flatback Heatsink xx2170	12.75	1.35	12	0.6
125632	12.75" Wide x 36" Flatback Heatsink xx2170	12.75	1.35	36	0.6



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125469	12.75" Wide x 12" Flatback Heatsink xx2044	12.75	2.25	12	0.56
125470	12.75" Wide x 36" Flatback Heatsink xx2044	12.75	2.25	36	0.56




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125475	13.381" Wide x 12" Flatback Heatsink xx5429	13.381	1.312	12	0.65
125476	13.381" Wide x 36" Flatback Heatsink xx5429	13.381	1.312	36	0.65




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125481	19.00" Wide x 36" Flatback Heatsink xx2016	19	1.32	12	0.65
125482	19.00" Wide x 36" Flatback Heatsink xx2016	19	1.32	36	0.65

## High Aspect


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125562	4.429" Wide x 11.81" High Aspect Heatsink 17080-11.81	4.429	3.276	11.81	0.59




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125565	6.818" Wide x 11.81" High Aspect Heatsink 19333-12	4.429	3.5	12	0.34



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122258	7.375" Wide x 12" High Aspect Extrusion 15817 xx5113	7.375	3.136	12	0.68
125649	7.375" Wide x 36" High Aspect Extrusion 15817 xx5113	7.375	3.136	36	0.68




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
122264	7.55" Wide x 12" High Aspect Extrusion 19832	7.55	2.8	12	0.34
125659	7.55" Wide x 36" High Aspect Extrusion 19832	7.55	2.8	36	0.34




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125571	10.08" Wide x 12" High Aspect Extrusion 21052	10.08	2.905	12	0.51
125572	10.08" Wide x 36" High Aspect Extrusion 21052	10.08	2.905	36	0.51

## SCR Press Pack Extrusions


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125526	5.00" Wide x 12" Presspack SCR Extrusion 16082 xx3560-2	5	2.25	12	1.4
125527	5.00" Wide x 36" Presspack SCR Extrusion 16082 xx3560-2	5	2.25	36	1.4




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125532	5.00" Wide x 12" Presspack SCR Extrusion 16565 xx5732	5	2.5	12	1.39
125533	5.00" Wide x 12" Presspack SCR Extrusion 16565 xx5732	5	2.5	36	1.39



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125538	7.00" Wide x 12" Presspack SCR Extrusion 16348 xx3559-2	7	3.125	12	0.85
125539	7.00" Wide x 36" Presspack SCR Extrusion 16348 xx3559-2	7	3.125	36	0.85



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125544	7.00" Wide x 12" Presspack SCR Extrusion 16235 xx5733	7	3.125	12	0.88
125545	7.00" Wide x 36" Presspack SCR Extrusion 16235 xx5733	7	3.125	36	0.88




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125550	9.80" Wide x 12" Presspack SCR Extrusion xx5735	9.8	2.85	12	0.71
125551	9.80" Wide x 36" Presspack SCR Extrusion xx5735	9.8	2.85	36	0.71




## Power Modules


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125556	4.921" Wide x 12" Power Module Extrusion 13698 xx5658	4.921	4.528	12	0.8
125557	4.921" Wide x 36" Power Module Extrusion 13698 xx5658	4.921	4.528	36	0.8




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125391	5.00" Wide x 12" Power Module Extrusion 19589 xx7331	5	1.38	12	3
125392	5.00" Wide x 36" Power Module Extrusion 19589 xx7331	5	1.38	36	3



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125379	5.00" Wide x 12" Power Module Extrusion 16414 xx7332	5	1.5	12	2.5
125380	5.00" Wide x 36" Power Module Extrusion 16414 xx7332	5	1.5	36	2.5




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125385	5.00" Wide x 12" Power Module Extrusion 16936 xx7330	5	2.5	12	1.7
125386	5.00" Wide x 36" Power Module Extrusion 16936 xx7330	5	2.5	36	1.7




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125613	7.52" Wide x 12" Power Module Extrusion 17003	7.52	5.3	12	0.65
125614	7.52" Wide x 36" Power Module Extrusion 17003	7.52	5.3	36	0.65

## DC/DC Heat Sink


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125361	1.45" Wide x 36" DC/DC Heatsink Extrusion 14363	1.45	0.768	12	4.2
125362	1.45" Wide x 36" DC/DC Heatsink Extrusion 14363	1.45	0.768	36	4.2




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125343	2.22" Wide x 12" DC/DC Heatsink Extrusion 14192	2.22	2.53	12	0.6
125344	2.22" Wide x 36" DC/DC Heatsink Extrusion 14192	2.22	2.53	36	0.6




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125355	2.28" Wide x 36" DC/DC Heatsink Extrusion 14362	2.28	0.455	12	4
125356	2.28" Wide x 12" DC/DC Heatsink Extrusion 14362	2.28	0.455	36	4



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125349	2.28" Wide x 12" DC/DC Heatsink Extrusion 14228	2.28	9.35	12	0.28
125350	2.28" Wide x 36" DC/DC Heatsink Extrusion 14228	2.28	9.35	36	0.28




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125331	2.40" Wide x 12" DC/DC Heatsink Extrusion 12613	2.4	0.9	12	4.1
125332	2.40" Wide x 36" DC/DC Heatsink Extrusion 12613	2.4	0.9	36	4.1




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125337	4.60" Wide x 12" DC/DC Heatsink Extrusion 12614	4.6	0.9	12	2.1
125338	4.60" Wide x 36" DC/DC Heatsink Extrusion 12614	4.6	0.9	36	2.1

## H Style/Mounting Shelf Heat Sinks


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125487	4.75" x 12" H Style Heatsink 4530 xx1024	4.75	1.245	12	2
125488	4.75" x 36" H Style Heatsink 4530 XX1024	4.75	1.245	36	2




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125493	4.75" x 12" H Style Heatsink 5410 xx1025	4.75	2.625	12	1.3
125494	4.75" x 36" H Style Heatsink 5410 xx1025	4.75	2.625	36	1.3



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125499	5.00" x 12" H Style Heatsink 6542 xx1245	5	5	12	0.72
125500	5.00" x 36" H Style Heatsink 6542 xx1245	5	5	36	0.72




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125505	6.25" Wide x 12" H Style Heatsink 16971 xx1541	6.25	6.25	12	0.59
125506	6.25" Wide x 36" H Style Heatsink 16971 xx1541	6.25	6.25	36	0.59




WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125637	4.702" Wide x 12" Mounting Shelf Extrusion 14264	4.702	3.312	12	1.8
125638	4.702" Wide x 12" Mounting Shelf Extrusion 14264	4.702	3.312	36	1.8

## BGA Style Heat Sinks


- Dimensions: Inches
- Thermal Resistance based on 3 Inch Length in Natural Convection Setting



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125283	1.10" Wide x 12" BGA Heatsink Extrusion 16240 xx8052-65	1.1	0.65	12	8
125284	1.10" Wide x 36" BGA Heatsink Extrusion 16240 xx8052-65	1.1	0.65	36	8



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125289	1.75" Wide x 12" BGA Heatsink Extrusion 16249 XX8260-65	1.75	0.65	12	7.8
125290	1.75" Wide x 36" BGA Heatsink Extrusion 16249 XX8260-65	1.75	0.65	36	7.8



WKV Part Number	Description	Width	Height	Length	Thermal Resistance °C/w/3"
125307	2.10" Wide x 12" BGA Heatsink Extrusion 12554 xx8355-100	2.1	1	12	3.8
125308	2.10" Wide x 36" BGA Heatsink Extrusion 12554 xx8355-100	2.1	1	36	3.8