

Home → Tool Types → Insert Bits → Spanner Insert Bit 2 Pack

Spanner Insert Bit 2 Pack



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Spanner Size	Price	Qty
71963	Spanner Insert Bit #4 x 25mm 2Pk	4		<input type="text" value="0"/>
71964	Spanner Insert Bit #6 x 25mm 2Pk	6		<input type="text" value="0"/>
71965	Spanner Insert Bit #8 x 25mm 2Pk	8		<input type="text" value="0"/>
71966	Spanner Insert Bit #10 x 25mm 2Pk	10		<input type="text" value="0"/>

Add to Cart

Details

Wiha Specialty Bits - Exact Fit Precision Machined
 Universal fit for all standard bit holders & power tools
 Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance

Additional Info

Head Type	☺☺ spanner
Country of Manufacture	Germany
Pack Quantity	2 Bits
Bit Drive Size	1/4" Hex
Bit Length	25mm~1"
ISO Standard Size	C6.3
Coating	Standard
Machine Hardness	HRC 59-61
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

You may also be interested in the following product(s)



Spanner Insert Bit 10 Pack

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
 CST USA**

1348 Dundas Cir,
 Monticello, MN 55362
 Customer Service Email:
cservice@wihatools.com
 Tel: 763-295-6591
 Fax: 763-295-6598

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

We accept

amazon pay

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter

Subscribe

© 2017 Wiha Tools USA. All Rights Reserved.

SHIPS FREE

