

Home → Tool Types → Power Bits → Torx® Power Bit 6" Single Pack

Torx® Power Bit 6" Single Pack







Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Torx Size	Pack Quantity	Price	Qty
74580	Torx® Power Bit T6 x 150mm (5.9")	T6	1 (sold individually)		<input type="text" value="0"/>
74582	Torx® Power Bit T7 x 150mm (5.9")	T7	1 (sold individually)		<input type="text" value="0"/>
74584	Torx® Power Bit T8 x 150mm (5.9")	T8	1 (sold individually)		<input type="text" value="0"/>
74585	Torx® Power Bit T9 x 150mm (5.9")	T9	1 (sold individually)		<input type="text" value="0"/>
74586	Torx® Power Bit T10 x 150mm (5.9")	T10	1 (sold individually)		<input type="text" value="0"/>
74587	Torx® Power Bit T15 x 150mm (5.9")	T15	1 (sold individually)		<input type="text" value="0"/>
74588	Torx® Power Bit T20 x 150mm (5.9")	T20	1 (sold individually)		<input type="text" value="0"/>
74589	Torx® Power Bit T25 x 150mm (5.9")	T25	1 (sold individually)		<input type="text" value="0"/>

SKU	Product	Torx Size	Pack Quantity	Price	Qty
74590	Torx® Power Bit T27 x 150mm (5.9")	T27	1 (sold individually)		0  
74591	Torx® Power Bit T30 x 150mm (5.9")	T30	1 (sold individually)		0  

Add to Cart



-  Add to Wishlist
  Share on Facebook
  Tweet This
  Pin it

We accept 

Details

Wiha premium bits - exact fit precision machined
 Universal fit for all standard bit holders & power tools
 Wiha special chrome-vanadium-molybdenum tool steel
 Torx is a 100% improvement in drive performance over other systems
 Virtually eliminates screw head cam-out
 Through hardened for best wear resistance


Additional Info

Head Type	  torx
Country of Manufacture	Germany
Pack Quantity	1 (sold individually)
Bit Drive Size	1/4" Hex
Bit Length	150mm~5.9"
ISO Standard Size	C6.3
Coating	Standard
Machine Hardness	HRC 59-61
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

You may also be interested in the following product(s)



Torx® Insert Bit 10 Pack

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

The Amazon Pay logo, featuring the word 'amazon pay' in a stylized font with the Amazon smile arrow above the 'a'.

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)